


PART No.	WIRE GA. / COLOR	"A"
0FNY0001ZXJ	#14 BLACK	203.2±5 (8.0)



DETAIL B



- NOTES:
1. MAX FUSE RATING: 20A, 32VDC.
  2. MAX. OPERATING TEMPERATURE: 80°C.
  3. WIRE: COPPER STRANDED, UL 1015.
  4. CONTACTS: C2680 ALLOY.
  5. CRIMP: MUST MEET USCAR 21 STANDARD.


UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CPK DENOTES CRITICAL CHARACTERISTICS.  
 CPK DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE  
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT IS TO BE DETERMINED BY THE DRAWING OR BY THE INSTRUCTIONS.  
 CPK DENOTES CP DIMENSIONS--MINIMUM CP VALUE DENOTES CP VALUE WITHIN THE DIMENSIONAL LIMITATIONS OF THE DRAWING AND INITIALLY LOCATED TO AROUND FOR MAXIMUM TOOL LIFE.

COPIES TO		MATERIAL SPEC		FINISH	
1	9	DRW	DWM	DATE	09/05/08
2	10	CHK		DATE	
3	12			DATE	
4	13			DATE	
5	14	APPD		DATE	
6	15			DATE	
7	16			DATE	
8	17			DATE	
				SCALE 1=1	
				SUPER DRW	
				RAW STK WT LBS/M	
				TOLERANCE UNLESS OTHERWISE SPECIFIED	
				TWO PLACE DEC ±.01	
				THREE PLACE DEC ±.005	
				ANGULAR ±1°	
				TITLE	
				FUSEHOLDER, IN LINE (WITH FUSE)	

LTR	REVISION	CHK	APD
A	000490ER-RELEASED 9/05/08		

REVISION	DRWG. NO.	OUTLINE
A	0FNY0001ZXJ	



UNCONTROLLED DOCUMENT