



NOTES:
 1. MATERIAL: SILICON RUBBER
 2. YELLOW COLOR
 3. 30 DURE HARD ©

METRIC
 COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
----	--------------	-------------	-------	-----

BILL OF MATERIAL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
 DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊕	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

COPIES TO	MATL SPEC	SEE NOTES	
1 9 18	FINISH N/A		
2 10 19	DRW E JIN	DATE 03/29/12	SCALE 1:1
3 12 20	CHK	DATE	SUPER DR
4 13 21	APPD	DATE	FINSH GOOD WT
5 14 23			GRAMS/PIECE
6 15 33			
7 16 43			
8 17 53			

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)									
DIMENSION	0.5	UP TO - 3	OVER 3 - 6	UP TO 6 - 30	OVER 30 - 120	UP TO 120 - 400			
TOLERANCE									

3RD ANGLE PROJECTION	TITLE #35 CABLE SEAL
----------------------	----------------------

Littelfuse® DES PLAINES, ILLINOIS 60016	REVISION A	DRWG. NO. OL-868-957
--------------------------------------------	---------------	-------------------------

											LTR	REVISION	CHK	APPD
											A	5047988EA NEW RELEASED E JIN		

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED