

SE-105 & SE-107 SETTINGS RECORD

Location: _____

Model Number: _____

Serial Number: _____

Ground-Fault Trip Level

Check One	GF Setting
<input type="checkbox"/>	4 A
<input checked="" type="checkbox"/>	2 A
<input type="checkbox"/>	0.5 A

Ground-Fault Trip Time

GF Trip Time(s) Setting

Output Contact Mode of Operation

Check One	MODE Setting
<input type="checkbox"/>	SH (Shunt Trip)
<input checked="" type="checkbox"/>	UV (Undervoltage Trip)

Current Transformer

Check One	
<input type="checkbox"/>	CT200, 56 mm (2.2") Inner Diameter
<input checked="" type="checkbox"/>	CT200L, 89 mm (3.5") Inner Diameter

Ground-Check Termination Device

Check One	
<input type="checkbox"/>	1N5339B Axial-Lead Termination Device, 5 W
<input checked="" type="checkbox"/>	SE-TA6 Termination Assembly, 50 W
<input type="checkbox"/>	SE-TA6-SM Stud-Mount Termination Device, 50 W
<input checked="" type="checkbox"/>	SE-TA6A-WL Termination Assembly with Wire Leads, 50 W
<input type="checkbox"/>	SE-TA6ASF Small-Format Termination Assembly, 12 W
<input checked="" type="checkbox"/>	SE-TA6ASF-WL Small-Format Termination Assembly with Wire Leads, 12 W

Remote Indication

Check One	
<input type="checkbox"/>	None
<input checked="" type="checkbox"/>	RK-13 Relay Interface Module
<input type="checkbox"/>	RK-102 Remote Indication and Reset Kit (22 mm)
<input checked="" type="checkbox"/>	RK-105 Remote Indication and Reset Assembly
<input type="checkbox"/>	RK-105I Remote Indication Assembly