

## 15-POLE SOCKETS & PLUGS



### Description

Members 15-Pole sockets and plugs are often used to support multiple connections within a trailer/vehicle's electrical system. Available in different wire guage sizes, as well as in different housing types and interfaces, this portfolio is meant to address normal and supplemental connection needs in your vehicle's wiring configuration.

### Web Resources

Download installation instructions, 2D prints and technical resources at: [littelfuse.com/15polesocketsplugs](http://littelfuse.com/15polesocketsplugs)

### Features and Benefits

- Plugs are equipped with locking lever and rollers to prevent accidental disconnection.
- Screw terminal versions especially suitable for spare & replacement parts markets.
- Mechanical resistance and watertightness guarantee an efficient and reliable electrical connection.

### Ordering Information

PART NUMBERS	DESCRIPTION	BODY MATERIAL	CABLE OUTLET	CABLE CORES ACCEPTED	ISO	NUMBER OF PINS	TERMINAL MATERIAL	TERMINALS	VOLTAGE
00594500	Plug	Plastic	15-17mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Crimped	24V
00594570	Plug	Plastic	11.5-14.5mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Crimped	24V
00594600	Plug	Plastic	15-17mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Screw	24V
00594670	Plug	Plastic	11.5-14.5mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Screw	24V
00584200	Socket	Plastic	15.5mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Screw	24V
00584300	Socket	Plastic	15.5mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Screw	24V
00584370	Socket	Plastic	7-12mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Screw	24V
00584400	Socket (90° Exit)	Plastic	15.5mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Screw	24V
00584500	Socket	Plastic	15.5mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Crimped	24V
00584600	Socket (90° Exit)	Plastic	15.5mm	12x1.5mm2, 3x2.5mm2	12098	15	Nickel-Plated Brass	Crimped	24V
00584700	Socket (Housing Only)	Plastic	—	—	12098	—	—	—	24V