

# Military Midget 10x38 mm Fuses

## 592 Series

Commercial Equivalent = [KLK Series](#)



### Description

With a vast network of manufacturing and engineering facilities and a global system of distribution channels, Littelfuse offers a variety of switchgear fuses to meet your specific needs, including military high-reliability fuses.

### Features & Benefits

| FEATURES                     | BENEFITS                                                                      |
|------------------------------|-------------------------------------------------------------------------------|
| <b>10x38 mm size</b>         | Common dimensions used in a variety of applications                           |
| <b>Fast-acting</b>           | Provides fast, reliable short-circuit response within the interrupting rating |
| <b>POWR-GARD® technology</b> | Ensures quality overcurrent protection                                        |

### Applications

- Control circuits
- Street and HID lighting
- Computers

### Approved to MIL-PRF-15160/60

| MIL TYPE DESIGNATION | NICKEL-PLATED CAPS | MIL TYPE DESIGNATION | NICKEL-PLATED CAPS |
|----------------------|--------------------|----------------------|--------------------|
| 60C 500V ¼A          | <b>592.125</b>     | F60C 500V 3A         | <b>592 003</b>     |
| F60C 500V ⅜A         | <b>592.200</b>     | F60C 500V 4A         | <b>592 004</b>     |
| F60C 500V ½A         | <b>592.250</b>     | F60C 500V 5A         | <b>592 005</b>     |
| F60C 500V ¾A         | <b>592.300</b>     | F60C 500V 6A         | <b>592 006</b>     |
| F60C 500V 1A         | <b>592.375</b>     | F60C 500V 8A         | <b>592 008</b>     |
| F60C 500V 1½A        | <b>592.500</b>     | F60C 500V 10A        | <b>592 010</b>     |
| F60C 500V 2A         | <b>592.750</b>     | F60C 500V 15A        | <b>592 015</b>     |
| F60C 500V 1A         | <b>592 001</b>     | F60C 500V 20A        | <b>592 020</b>     |
| F60C 500V 1½A        | <b>592 015</b>     | F60C 500V 25A        | <b>592 025</b>     |
| F60C 500V 2A         | <b>592 002</b>     | F60C 500V 30A        | <b>592 030</b>     |

Note: Boldface numbers indicate series; light type numbers indicate amperage value.

**Disclaimer Notice** – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/product-disclaimer](http://www.littelfuse.com/product-disclaimer).