

[HOME \(HTTPS://WWW.CSAGROUP.ORG/\)](https://www.csagroup.org/) / [TESTING AND CERTIFICATION \(HTTPS://WWW.CSAGROUP.ORG/TESTING-CERTIFICATION/\)](#) / [CSA GROUP PRODUCT LISTING \(HTTPS://WWW.CSAGROUP.ORG/TESTING-CERTIFICATION/PRODUCT-LISTING/\)](#) / [CERTIFICATION RECORD](#)

[Contact an Expert \(https://www.csagroup.org/contact/\)](https://www.csagroup.org/contact/)

# Certification Record

| CUSTOMER   | CLASS  | FILE NUMBER  |
|--|--|--------------|
| Littelfuse, Inc.<br>8755 W. Higgins Rd Suite 500,<br>Chicago<br>Illinois<br>United States<br>60631 | <a href="#">6225-01 (.../class/?class=6225-01)</a><br>FUSEHOLDER ASSEMBLIES- | 047574_0_000 |

Cartridge Fuseholder Assemblies, Cat. Nos. 800-01/816, 803-01/816 are rated 16 A, 500 V ac.

All other catalog numbers, 16 A, 250 Vac, miniature extractor type, single pole.

| Fuseholder | Fuse Size   | Fuse Cap |
|------------|-------------|----------|
| 800        | 5 x 20 mm   | 815      |
| 800        | 6.3 x 32 mm | 816      |
| 801        | 5 x 20 mm   | 815      |
| 801        | 6.3 x 32 mm | 816      |
| 802        | 5 x 20 mm   | 815      |

|        |             |                    |
|--------|-------------|--------------------|
| 802    | 6.3 x 32 mm | 816                |
| 800-01 | 6.3 x 32 mm | 816                |
| 803-01 | 6.3 x 32 mm | 816                |
| 810    | 5 x 20 mm   | 815                |
| 810    | 6.3 x 32 mm | 816                |
| 811    | 5 x 20 mm   | 815                |
| 811    | 6.3 x 32 mm | 816                |
| 813    | 6.3 x 32 mm | 816                |
| 813    | 5 x 20 mm   | 815                |
| 814    | 5 x 20 mm   | 815                |
| 814    | 6.3 x 32 mm | 816                |
| 830    | 5 x 20 mm   | 835 or 837         |
| 831    | 5 x 20 mm   | 835 or 837         |
| 820    | 5 x 20 mm   | 835, 835-20 or 837 |
| 820-20 | 5 x 20 mm   | 835, 835-20 or 837 |
| 821    | 5 x 20 mm   | 835, 835-20 or 837 |
| 821-20 | 5 x 20 mm   | 835, 835-20 or 837 |
| 823    | 5 x 20 mm   | 835, 835-20 or 837 |
| 824    | 5 x 20 mm   | 835, 835-20 or 837 |
| 834    | 5 x 20 mm   | 835, 835-20 or 837 |

Contact an Expert  
[\(https://www.csagroup.org/contact/\)](https://www.csagroup.org/contact/)

These devices are either circuit board mounted extractor type or 3/16 in wide 1/2 quick-connect 1/2 type fuseholders or soldered connections intended for use with the following miniature fuses, and fuse caps.

Fuseholder Cat. Nos. 800, 801 and 802 are intended for through-panel mounting and are provided with a mounting nut.

These devices are Certified as components for use only in other Certified equipment when the suitability of the combination is to be determined by CSA Group.

Notes:

1. These fuseholders are for use with supplemental type fuses.
2. The type designations may be completed with suffixes for mechanical details.
3. The spacings from live parts of the fuseholder to the grounded or dead metal parts of the equipment shall be in accordance with the requirements of the equipment in which the fuseholders are installed.

- 4. The suitability of the mounting means shall be determined in the end use application.
- 5. The suitability of connections to the terminals including temperature rating and the use of "quick-connect" terminals shall be determined in the end use application.

/ld

Contact an Expert

# We're always here to help. Let's talk.

We're here to answer your questions and help you get started right away. Call or send us a message anytime.

Contact an Expert  
(<https://www.csagroup.org/contact/>)

[Contact Us \(https://www.csagroup.org/contact\)](https://www.csagroup.org/contact)



**CSA GROUP**

[FAQs \(/faq/\)](/faq/)

[CSA OnDemand™](https://www.csagroup.org/store.csagroup.org/ondemand/s/?language=en_US)

([https://www.csagroup.org/store.csagroup.org/ondemand/s/?language=en\\_US](https://www.csagroup.org/store.csagroup.org/ondemand/s/?language=en_US))

[Informs & Notices \(/informs-notices/\)](/informs-notices/)

[Submit an Incident Report \(/submit-a-report\)](/submit-a-report)

[Product Alerts & Recalls \(/product-alerts-recalls/\)](/product-alerts-recalls/)

[Report Suspect Counterfeit Marks \(/testing-certification/marks-labels/brand-protection/reporting-suspect-counterfeit-marks\)](/testing-certification/marks-labels/brand-protection/reporting-suspect-counterfeit-marks)

[Sign up for our Newsletter \(https://www.csagroup.org/newsletter\)](https://www.csagroup.org/newsletter)

<http://www.facebook.com/CSAGroup>  
<http://www.linkedin.com/company/13516287>  
<https://www.youtube.com/channel/UC13516287>

[Agreement on Acceptance of Components \(/agreement-acceptance-components/\)](#)

[Resources & Insights \(/resources-insights/\)](#)

[Standards Research \(/standards/standards-research/\)](#)

[CSA Communities \(http://community.csagroup.org/login.jspa?referer=%252Findex.jspa\)](http://community.csagroup.org/login.jspa?referer=%252Findex.jspa)

[CSA Group Product Listing \(/testing-certification/product-listing/\)](#)

Contact an Expert  
[\(https://www.csagroup.org/contact/\)](https://www.csagroup.org/contact/)

[Legal \(https://www.csagroup.org/legal/\)](https://www.csagroup.org/legal/)

[Privacy Policy \(https://www.csagroup.org/legal/privacy-policy/\)](https://www.csagroup.org/legal/privacy-policy/)

[Evidence of Insurance \(https://www.csagroup.org/legal/evidence-of-insurance/\)](https://www.csagroup.org/legal/evidence-of-insurance/)

[HSE Policy \(https://www.csagroup.org/hse-policy/\)](https://www.csagroup.org/hse-policy/)

[Accreditation \(https://www.csagroup.org/accreditation/\)](https://www.csagroup.org/accreditation/)

[Accessibility \(https://www.csagroup.org/accessibility/\)](https://www.csagroup.org/accessibility/)

[Annual Report \(https://www.csagroup.org/annual-report/\)](https://www.csagroup.org/annual-report/)

© 2020 [CSA Group](https://www.csagroup.org)  
[\(https://www.csagroup.org\)](https://www.csagroup.org)