

ZCASE® SMZ SERIES STUD-MOUNT FUSE HOLDER



Description

The Littelfuse 80V Bolt-Down ZCASE® SMZ Series Stud-Mount Fuse Holder reduces the need for wiring and parts by allowing ZCASE® single high-current fuses to be directly installed on an alternator, battery switch, or electrical relay. Thanks to an insulated M8 stud on the busbar, the compatible fuse (sold separately) and output cable with a ring terminal (not included) can be assembled using the included standard M8 nut. There's no need to buy a specialized nylon nut.

The SMZ Series fuse holder is available with an M6, M8, or M10 mounting hole to meet the requirements of various applications. Various configurations, including a protective cover for the fuse only, with a protective cover for the fuse and mounting stud, and without a cover, are available.

Applications

- Alternator, Battery Switch, or Electrical Relay Fusing

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/smz

Ordering Information

PART NUMBER	DESCRIPTION	CURRENT RATING MAX	FUSE TYPE	MOUNTING METHOD	MAX VOLTAGE RATING
OFHZ0201Z	32V Bolt-Down ZCASE® SMZ Series Stud-Mount Fuse Holder with M8 Mounting Hole and Fuse & Stud Cover	400A	ZCASE	M8 Stud Mount	32V
OFHZ0202Z	32V Bolt-Down ZCASE® SMZ Series Stud-Mount Fuse Holder with M8 Mounting Hole and Fuse Cover	400A	ZCASE	M8 Stud Mount	32V
OFHZ0211Z	32V Bolt-Down ZCASE® SMZ Series Stud-Mount Fuse Holder with M10 Mounting Hole and Fuse & Stud Cover	400A	ZCASE	M10 Stud Mount	32V
OFHZ0212Z	32V Bolt-Down ZCASE® SMZ Series Stud-Mount Fuse Holder with M10 Mounting Hole and Fuse Cover	400A	ZCASE	M10 Stud Mount	32V
OFHZ0231Z	32V Bolt-Down ZCASE® SMZ Series Stud-Mount Fuse Holder with M6 Mounting Hole and Fuse & Stud Cover	400A	ZCASE	M6 Stud Mount	32V
OFHZ0232Z	32V Bolt-Down ZCASE® SMZ Series Stud-Mount Fuse Holder with M6 Mounting Hole and Fuse Cover	400A	ZCASE	M6 Stud Mount	32V
OFHZ0233Z	32V Bolt-Down ZCASE® SMZ Series Stud-Mount Fuse Holder with M6 Mounting Hole	400A	ZCASE	M6 Stud Mount	32V
901-524	ZCASE® SMZ Series Fuse Holder Cover for Fuse Only	-	-	-	-
901-525	ZCASE® SMZ Series Fuse Holder Cover for Fuse & Stud	-	-	-	-
OFHZ0241Z	SMZ M10 Fuse Holder	400A	ZCASE	M10 Stud Mount	80V
901-541	SMZ M10 Fuse Cover	-	-	-	-

Specifications

Agency Approval - Shock:	ISO16750-3 Section 4.2.2.2
Agency Approval - Vibration:	ISO16750-3 4.1.2.7
Current Rating Continuous:	400A
Current Rating Max:	400A
Current Rating Max Terminal:	400A
Fuse Type:	ZCASE
Humidity:	SAE J1455 2006 10% ~ 98% RH
Input Terminals:	M6, M8, M10 Stud Mount Hole
Mounting Method:	M6, M8, M10 Stud Mount
Output Terminals:	M8 Stud
Recommended Torque:	M8 Nut: 14±2 Nm
Temperature in Celsius:	Operation temperature: -40 °C ~ +105 °C Storage temperature: -55 °C ~ 125 °C
Temperature in Fahrenheit:	Operation temperature: -40 °F ~ +221 °F Storage temperature: -67 °F ~ 257 °F
Max Voltage Rating:	32V, 80V
Application Notes	Fuse must not exceed 70% of rated current UL rating belongs to the red cover and not to the entire assembly.

Features And Benefits

- Accepts Littelfuse high-current ZCASE® single bolt-down M8-size fuses (sold separately)
- Available mounting hole sizes include M6, M8, and M10
- Up to 3 SMZ Series fuse holders can be stacked to protect multiple circuits
- Space-saving design eliminates the need to wire in a separate fuse holder or power distribution module (PDM)
- Tin-plated copper busbar offers corrosion resistance
- Red UL 94 V-0 rated cover is offered in 2 styles to provide protection from accidental contact - one option covers the fuse only, while the other option covers the fuse and the mounting stud
- Total continuous current should not exceed 400A per holder