

55075 Series

Stainless Steel M12 Geartooth Speed Sensor

RoHS



Additional Information



Resources




Accessories




Samples

Dimensions

Dimensions in mm (inch)



Block Diagram



Description

The 55075 is a robust stainless steel hall effect barrel sensor with an M12 x 1mm pitch thread, 46mm (1.810") long primarily for geartooth speed sensing. It protects against severe and automotive environments and is capable of switching up to 27Vdc and 25mA. It is available as three-wire (voltage output) version with a range of sensitivity, cable length and connector options. It is ideally suited to wheel, transmission and cam shaft speed sensing, geartooth sensor, rotary encoders, industrial, commercial, and automotive applications.


Features & Benefits

- Ferrous target geartooth speed sensor
- Stainless steel M12 threaded barrel
- Electronic protection against severe and automotive environments
- Self adjusting magnetic range
- Three-wire (voltage output)
- EMC Protection (Consult Littelfuse)
- Short circuit/reverse voltage protection
- Long life, up to 20 billion operations
- High speed operation
- No chopper delay
- Unaffected by harsh environments
- Rotary orientation not critical
- On-chip 10-bit A/D converter
- IP67 rated

Applications

- Geartooth sensor
- Camshaft sensor
- Linear encoder
- Rotary encoder

Application Example - Geartooth Sensor



55075 Series

Stainless Steel M12 Geartooth Speed Sensor

Electrical Ratings


| Hall Type | | | Digital Switch 3-Wire (Voltage Output) |
|-------------------------------------|------------------------|------------|---|
| Supply Voltage ¹ | Operate | Vdc | 4.75 to 25.2 |
| | Reverse Voltage | | -25 |
| | Overvoltage Protection | Vdc - max. | 27 |
| Output High Voltage | | Vdc (max) | VDD - 2 (sinking output w/internal pull-up resistor) |
| Output Low Voltage | | Vdc (max) | 0.6 @ 25mA |
| Output Current (continuously on) | | mA (max) | 25 |
| Current Consumption | | mA (min) | 1.0 |
| | | mA (max) | 6.0 |
| Switching Speed | | kHz (max) | 15 |
| Temperature | Operating | °C | -40 to +125 |

Note: 1. As long as Tj (Junction Temperature) is not exceeded.


Cable Length Options

| Cable Type: 24 AWG 7/32 PVC 105°C Double Insulated | |
|--|---------------------------|
| Select Option | Cable Length mm (inch) |
| 02 | 300 (11.81) |

Termination Options

| Select Option | Description | |
|---------------|--------------|---|
| A | Tinned Leads |  |

Part Numbering System



Packaging

| Packaging Option | Packaging Specification | Quantity | Quantity & Packaging Code | Taping Width |
|------------------|-------------------------|----------|---------------------------|--------------|
| Bulk | Bulk | 500 | N/A | N/A |

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.