

# ATO® AFH SERIES

## 32V IN-LINE WIRE-LEADED PANEL-MOUNT FUSE HOLDER



### Description

The ATO® AFH Series 32V In-Line Wire-Leaded Panel-Mount Fuse Holder can be used for either in-line installation or panel-mounting applications thanks to the 8" looped lead wire and the snap fit gripping arms.

Designed with a 14 AWG black lead wire, the ATO® AFH Series fuse holder is compatible with ATO® blade-style fuses (sold separately) up to 20 amps. The interlocking, heat-stabilized nylon fuse holder body allows you to snap multiple fuse holders together.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/AFHFuseHolders](http://littelfuse.com/AFHFuseHolders)

### Applications

- Heavy-Duty Automotive Fusing

### Features and Benefits

- Accepts ATO® blade-style fuses (sold separately) up to 20 amps
- Interlocking fuse holder body lets you connect multiple fuse holders
- Heat-stabilized black nylon body has a UL 94 V-2 flammability rating
- 8" looped 14 AWG black lead wire allow simple in-line installation
- Gripping arms enable optional panel mounting

### Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
0AFH0001XP W/O FUSE	32V In-Line Wire-Leaded Panel-Mount Fuse Holder - 20A, 14 AWG - Blister Pack - 100 Pcs.	ATO	IN LINE FUSE HOLDER	20 Amps	32 VDC
0AFH0001Z W/O FUSE	32V In-Line Wire-Leaded Panel-Mount Fuse Holder - 20A, 14 AWG	ATO	IN LINE FUSE HOLDER	20 Amps	32 VDC

### Specifications

<b>Continuous Current Rating:</b>	15A
<b>Max Current Rating:</b>	20A
<b>Max Current Rating Terminal:</b>	20A
<b>Fuse Type:</b>	ATO®
<b>Ignition Protection:</b>	V-2
<b>Ignition-Proof:</b>	UL 94
<b>Input Terminals:</b>	ATO FUSE BLADES
<b>Mounting Method:</b>	IN LINE FUSE HOLDER
<b>Output Terminals:</b>	WIRE WITH TERMINALS INCLUDED
<b>Max Voltage Rating:</b>	32 VDC
<b>Wire Description:</b>	VINYL PLASTIC INSULATED ANNEALED COPPER CABLE
<b>Wire Size:</b>	14 AWG

### PN: 0AFH0001XP

The ATO® AFH Series 32V In-Line Wire-Leaded Panel-Mount Fuse Holder can be used for either in-line installation or panel-mounting applications thanks to the 8" looped lead wire and the snap fit gripping arms. This configuration (0AFH0001XP) is rated for up to 20-amp ATO® blade fuses (sold separately) and features a black 14 AWG looped lead wire. Carded blister packaging allows simple retail display.

### Features and Benefits

- Accepts ATO® blade-style fuses (sold separately) up to 20 amps
- Black 14 AWG looped lead wire
- Carded blister packaging for easy retail display

### PN: 0AFH0001Z

The ATO® AFH Series 32V In-Line Wire-Leaded Panel-Mount Fuse Holder can be used for either in-line installation or panel-mounting applications thanks to the 8" looped lead wire and the snap fit gripping arms. This configuration (0AFH0001Z) is rated for up to 20-amp ATO® blade fuses (sold separately) and features a black 14 AWG looped lead wire.

### Features and Benefits

- Accepts ATO® blade-style fuses (sold separately) up to 20 amps
- Black 14 AWG looped lead wire