


RATINGS:			
MAXIMUM VOLTAGE	600 Vac		
MAXIMUM CURRENT	30 mA		
RESISTANCE	20 kΩ		
THERMAL:			
600 Vac	6 MINUTES ON		
	60 MINUTES OFF		
420 Vac	CONTINUOUS		



- NOTES:
- DIMENSIONS IN MILLIMETERS [INCHES]
 - TERMINAL-BLOCK SCREWS: 6-32 X 0.25
 - MOUNTING SCREWS: M4 OR 8-32
 - ON REVISION 2 UNITS ENCLOSURE IS ELECTRICALLY CONNECTED TO TERMINAL G THROUGH JUMPER FROM TERMINAL G TO ⊕ SCREW. THIS CONNECTION MAY BE REMOVED FOR DIELECTRIC STRENGTH TESTING. ENSURE THAT THE JUMPER IS INSTALLED AFTER TESTING.
 - ON REVISION 1 UNITS, ⊕ SCREW IS NOT PRESENT AND ENCLOSURE IS ELECTRICALLY CONNECTED TO TERMINAL G.
 - NOT ALL CERTIFICATIONS SHOWN.