

| REVISION | | |
|----------|--------|-------------------------|
| REV | DATE | DESCRIPTION |
| A | 9/2/22 | 525636GCP - RELEASE MRY |

SPECIFICATIONS:



VOLTAGE RATING: 600VAC/DC

AMP RATING: 30 AMPERES

INTERRUPT RATING: 200kA

WIRE RANGE: (1) 0.75-10mm² 2.0-2.5 Nm
18-8 AWG 18-22 lb-in
(2) 0.75-10mm² 2.0-2.5 Nm
18-6 AWG 18-22 lb-in
(1) 6-4 AWG 22-26 lb-in

APPROVALS: UL LISTED (E14721)
CSA CERTIFIED

| | | | | |
|---|--|---------------|-------------------------------|--------------|
| 1 | | | | |
| NO | COMPONENT NO | DESCRIPTION | QTY/M | U/M |
| BILL OF MATERIAL | | | | |
| <S> | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE | | | |
| ● | DENOTES CRITICAL CHARACTERISTICS. | | | |
| CPK | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE | | | |
| ⊠ | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. | | | |
| CP | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. | | | B |
| MATL SPEC | | FINISH | | |
| DRW JMOLER | DATE 8/24/2022 | SCALE NTS | FINISH GOOD WT GRAMS/PIECE | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 | | | | |
| 3RD ANGLE PROJECTION  | | | | |
| TITLE LFPSC003 OUTLINE | | | | |
|  Littelfuse® CHICAGO, ILLINOIS 60631 | | REVISION A | DRWG NO. OL-LFPSC003 | SHEET 1 OF 1 |