


# HiperFET™

## Power MOSFET

### Q3-Class

## IXFB44N100Q3


N-Channel Enhancement Mode  
Fast Intrinsic Rectifier



$$\begin{aligned} V_{DSS} &= 1000V \\ I_{D25} &= 44A \\ R_{DS(on)} &\leq 220m\Omega \\ t_{rr} &\leq 300ns \end{aligned}$$

| Symbol     | Test Conditions                                                    | Maximum Ratings |            |
|------------|--------------------------------------------------------------------|-----------------|------------|
| $V_{DSS}$  | $T_J = 25^\circ C$ to $150^\circ C$                                | 1000            | V          |
| $V_{DGR}$  | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GS} = 1M\Omega$          | 1000            | V          |
| $V_{GSS}$  | Continuous                                                         | $\pm 30$        | V          |
| $V_{GSM}$  | Transient                                                          | $\pm 40$        | V          |
| $I_{D25}$  | $T_C = 25^\circ C$                                                 | 44              | A          |
| $I_{DM}$   | $T_C = 25^\circ C$ , Pulse Width Limited by $T_{JM}$               | 110             | A          |
| $I_A$      | $T_C = 25^\circ C$                                                 | 44              | A          |
| $E_{AS}$   | $T_C = 25^\circ C$                                                 | 4               | J          |
| $dv/dt$    | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ C$ | 50              | V/ns       |
| $P_D$      | $T_C = 25^\circ C$                                                 | 1560            | W          |
| $T_J$      |                                                                    | -55 ... +150    | $^\circ C$ |
| $T_{JM}$   |                                                                    | 150             | $^\circ C$ |
| $T_{stg}$  |                                                                    | -55 ... +150    | $^\circ C$ |
| $T_L$      | 1.6mm (0.062 in.) from Case for 10s                                | 300             | $^\circ C$ |
| $T_{SOLD}$ | Plastic Body for 10s                                               | 260             | $^\circ C$ |
| $F_C$      | Mounting Force                                                     | 30..120/6.7..27 | N/lb.      |
| Weight     |                                                                    | 10              | g          |

### PLUS264™



G = Gate      D = Drain  
S = Source      Tab = Drain

### Features

- Low Intrinsic Gate Resistance
- Low Package Inductance
- Fast Intrinsic Rectifier
- Low  $R_{DS(on)}$  and  $Q_G$

### Advantages

- High Power Density
- Easy to Mount
- Space Savings

### Applications

- DC-DC Converters
- Battery Chargers
- Switch-Mode and Resonant-Mode Power Supplies
- DC Choppers
- Temperature and Lighting Controls

| Symbol       | Test Conditions<br>( $T_J = 25^\circ C$ Unless Otherwise Specified) | Characteristic Values |      |                    |
|--------------|---------------------------------------------------------------------|-----------------------|------|--------------------|
|              |                                                                     | Min.                  | Typ. | Max.               |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 3mA$                                         | 1000                  |      | V                  |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 8mA$                                     | 3.5                   |      | 6.5 V              |
| $I_{GSS}$    | $V_{GS} = \pm 30V$ , $V_{DS} = 0V$                                  |                       |      | $\pm 200$ nA       |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 125^\circ C$           |                       |      | 50 $\mu A$<br>3 mA |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                 |                       |      | 220 m $\Omega$     |


| Symbol       | Test Conditions<br>( $T_J = 25^{\circ}\text{C}$ Unless Otherwise Specified)                                                                          | Characteristic Values |      |                          |
|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|--------------------------|
|              |                                                                                                                                                      | Min.                  | Typ. | Max.                     |
| $g_{fs}$     | $V_{DS} = 20\text{V}$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                                                                                           | 26                    | 43   | S                        |
| $C_{iss}$    | $V_{GS} = 0\text{V}$ , $V_{DS} = 25\text{V}$ , $f = 1\text{MHz}$                                                                                     |                       | 13.6 | nF                       |
| $C_{oss}$    |                                                                                                                                                      |                       | 1046 | pF                       |
| $C_{rss}$    |                                                                                                                                                      |                       | 86   | pF                       |
| $R_{Gi}$     | Gate Input Resistance                                                                                                                                |                       | 0.12 | $\Omega$                 |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 \cdot I_{D25}$<br>$R_G = 0.5\Omega$ (External) |                       | 48   | ns                       |
| $t_r$        |                                                                                                                                                      |                       | 30   | ns                       |
| $t_{d(off)}$ |                                                                                                                                                      |                       | 66   | ns                       |
| $t_f$        |                                                                                                                                                      |                       | 28   | ns                       |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 \cdot I_{D25}$                                                                     |                       | 264  | nC                       |
| $Q_{gs}$     |                                                                                                                                                      |                       | 76   | nC                       |
| $Q_{gd}$     |                                                                                                                                                      |                       | 110  | nC                       |
| $R_{thJC}$   |                                                                                                                                                      |                       |      | $0.08^{\circ}\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                                      | 0.13                  |      | $^{\circ}\text{C/W}$     |

## Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^{\circ}\text{C}$ Unless Otherwise Specified)                           | Characteristic Values |      |               |
|----------|-------------------------------------------------------------------------------------------------------|-----------------------|------|---------------|
|          |                                                                                                       | Min.                  | Typ. | Max.          |
| $I_s$    | $V_{GS} = 0\text{V}$                                                                                  |                       |      | 44 A          |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$                                                           |                       |      | 176 A         |
| $V_{SD}$ | $I_F = I_s$ , $V_{GS} = 0\text{V}$ , Note 1                                                           |                       |      | 1.4 V         |
| $t_{rr}$ | $I_F = 22\text{A}$ , $-di/dt = 100\text{A}/\mu\text{s}$<br>$V_R = 100\text{V}$ , $V_{GS} = 0\text{V}$ |                       |      | 300 ns        |
| $Q_{RM}$ |                                                                                                       |                       | 2.1  | $\mu\text{C}$ |
| $I_{RM}$ |                                                                                                       |                       | 16.2 | A             |

Note 1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .

## PLUS264™ (IXFB) Outline









| SYM | INCHES   |       | MILLIMETERS |       |
|-----|----------|-------|-------------|-------|
|     | MIN      | MAX   | MIN         | MAX   |
| A   | .185     | .209  | 4.70        | 5.31  |
| A1  | .102     | .118  | 2.59        | 3.00  |
| b   | .037     | .055  | 0.94        | 1.40  |
| b1  | .087     | .102  | 2.21        | 2.59  |
| b2  | .110     | .126  | 2.79        | 3.20  |
| c   | .017     | .029  | 0.43        | 0.74  |
| D   | 1.007    | 1.047 | 25.58       | 26.59 |
| E   | .760     | .799  | 19.30       | 20.29 |
| e   | .215 BSC |       | 5.46 BSC    |       |
| L   | .779     | .842  | 19.79       | 21.39 |
| L1  | .087     | .102  | 2.21        | 2.59  |
| Q   | .240     | .256  | 6.10        | 6.50  |
| Q1  | .330     | .346  | 8.38        | 8.79  |
| ØR  | .155     | .187  | 3.94        | 4.75  |
| ØR1 | .085     | .093  | 2.16        | 2.36  |

## ADVANCE TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

|                                                                                  |           |           |           |           |              |              |              |              |              |             |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
|                                                                                  | 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |

**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$** 

**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 22\text{A}$  Value vs. Junction Temperature**

**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 22\text{A}$  Value vs. Drain Current**

**Fig. 6. Maximum Drain Current vs. Case Temperature**









**Fig. 7. Input Admittance**

**Fig. 8. Transconductance**

**Fig. 9. Forward Voltage Drop of Intrinsic Diode**

**Fig. 10. Gate Charge**

**Fig. 11. Capacitance**

**Fig. 12. Forward-Bias Safe Operating Area**


Fig. 13. Maximum Transient Thermal Impedance





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).