




## SPDN Series

Surge protective devices (SPDs) provide equipment protection from transient overvoltage events lasting micro-seconds. By limiting the overvoltage to the equipment during these events, costly damage and downtime can be mitigated.

The NEMA-style SPDN series for external panel mount is available for 120 V to 480 V nominal voltage sub-distribution board applications.

.....  
Please check all applicable specifications prior to making a product substitution or selection. For special applications or more complete information, visit [Littelfuse.com/SPDN](http://Littelfuse.com/SPDN) or contact us at **1-800-832-3873**.



## SPDN-A and SPDN-B Series

| Series/Model                            | Littelfuse<br>SPDN-A           | Littelfuse<br>SPDN-B | Schneider/ASCO<br>425 | Eaton<br>SPC | Mersen<br>STXP   | Southern Tier<br>450 | Ilsco/SSI<br>XE  |
|-----------------------------------------|--------------------------------|----------------------|-----------------------|--------------|------------------|----------------------|------------------|
| <b>Surge Current Ratings (per mode)</b> | 65 kA                          | 65 kA                | 50 kA                 | 100 kA       | 50 kA            | 25 kA                | 100 kA           |
| <b>SPD Technology</b>                   | Pill Stack                     | Pill Stack           | TPMOV                 | TPMOV        | TPMOV            | PTMOV                | TPMOV            |
| <b>Nominal Discharge Current (8/20)</b> | 20 kA                          | 20 kA                | 20 kA                 | 20 kA        | 20 kA            | 20 kA                | 20 kA            |
| <b>UL 1449 SPD Type</b>                 | Type 1 or 2                    | Type 1               | Type 1                | Type 1 or 2  | Type 1           | Type 2               | Type 1 or Type 2 |
| <b>MCOV (120 V model)</b>               | 150 V                          | 150 V                | 150 V                 | 150 V        | 150 V            | 150 V                | 150 V            |
| <b>VPR (L-N 120 V model)</b>            | 700 V                          | 700 V                | 700 V                 | 700 V        | 700 V            | 700 V                | 700 V            |
| <b>Modes of Protection</b>              | All                            | All                  | All                   | All          | All              | All                  | All              |
| <b>SCCR</b>                             | 200 kA                         | 200 kA               | 200 kA                | 200 kA       | 200 kA           | 200 kA               | 200 kA           |
| <b>Connection Type</b>                  | Wired                          | Wired                | Wired                 | Wired        | Wired            | Wired                | Wired            |
| <b>Encloser Type (standard)</b>         | NEMA 4X                        | NEMA 4X              | NEMA 4X               | NEMA 4X      | NEMA 4X          | NEMA 4X              | NEMA 4X          |
| <b>Indicator Lights</b>                 | 1 per phase                    | 1 per phase          | 1 per phase           | 1 per phase  | 2 LEDs per phase | Single               | 1 per phase      |
| <b>Audible Alarm</b>                    | Yes                            | Yes                  | Yes                   | Optional     | Yes              | No                   | Optional         |
| <b>Form C Dry Contacts</b>              | Yes                            | Yes                  | Yes                   | Optional     | Yes              | Yes                  | Optional         |
| <b>EMI/RFI Filtering</b>                | Optional                       | No                   | No                    | Optional     | No               | Yes                  | Optional         |
| <b>Ground Reference Monitoring</b>      | N-G Voltage > 20 V<br>Detected | No                   | No                    | No           | No               | No                   | No               |



## SPDN-C and SPDN-D Series

| Series/Model                            | Littelfuse<br>SPDN-C | Littelfuse<br>SPDN-D | Schneider/ASCO<br>420 | Mersen<br>STXR | Ilsco/SSI<br>SE  | Citel<br>M50     |
|-----------------------------------------|----------------------|----------------------|-----------------------|----------------|------------------|------------------|
| <b>Surge Current Ratings (per mode)</b> | 50 kA                | 50 kA                | 50 kA                 | 50 kA          | 100 kA           | 50 kA            |
| <b>SPD Technology</b>                   | Pill Stack           | Pill Stack           | TPMOV                 | TPMOV          | TPMOV            | TMOV + GSG       |
| <b>Nominal Discharge Current (8/20)</b> | 20 kA                | 20 kA                | 20 kA                 | 20 kA          | 20 kA            | 20 kA            |
| <b>UL 1449 SPD Type</b>                 | Type 1               | Type 1               | Type 1                | Type 1         | Type 1 or Type 2 | Type 1 or Type 2 |
| <b>MCOV (120 V model)</b>               | 150 V                | 150 V                | 150 V                 | 150 V          | 150 V            | 150 V            |
| <b>VPR (L-N 120 V model)</b>            | 600 V                | 600 V                | 600 V                 | 700 V          | 700 V            | 700 V            |
| <b>Modes of Protection</b>              | Reduced              | Reduced              | Reduced               | Reduced        | Reduced          | Reduced          |
| <b>SCCR</b>                             | 200 kA               | 200 kA               | 200 kA                | 200 kA         | 200 kA           | 200 kA           |
| <b>Connection Type</b>                  | Wired                | Wired                | Wired                 | Wired          | Wired            | Wired            |
| <b>Encloser Type (standard)</b>         | NEMA 4X              | NEMA 4X              | NEMA 4X               | NEMA 4X        | NEMA 4X          | NEMA 6           |
| <b>Indicator Lights</b>                 | 1 per phase          | 1 per phase          | Single                | Single         | Single           | 1 per phase      |
| <b>Audible Alarm</b>                    | Yes                  | No                   | Yes                   | Optional       | Optional         | Yes              |
| <b>Form C Dry Contacts</b>              | Yes                  | No                   | Yes                   | Optional       | Optional         | No               |
| <b>EMI/RFI Filtering</b>                | No                   | No                   | No                    | No             | Optional         | Optional         |

Disclaimer Notice—Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/product-disclaimer](http://www.littelfuse.com/product-disclaimer).