




NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY
2. MATERIAL: BODY -- MAPEX UL94 -V0, BLACK
M8 x 1.25 STUD -- SAE1215/DIN 9SMn28/11SMn30 STEEL, ZINC PLATED
3. MAXIMUM MOUNTING TORQUE FOR M4 MOUNTING HOLES 10 N*M, 7.4 LBF*FT
4. MAXIMUM TORQUE FOR M8 STUD 8.9-13.3 LBF*FT, 12-18 N*m

METRIC
ASSEMBLY



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES									
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.									
© DENOTES CRITICAL CHARACTERISTICS.									
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE									
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS									
CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE									

2	STUD	1	EA
1	BODY	1	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M
BILL OF MATERIAL			

LTR	COPIES TO		MATL SPEC		SEE NOTE 2	
	1	9	18	FINISH		
DATE	2	10	19	DRW	PVN	SCALE
	3	12	20	CHK	DATE	03/21/12
REVISION	4	13	21	APPD	DATE	03/21/12
	5	14	23	FINISH GOOD WT		
CHK	6	15	33	GRAMS/PIECE		
	7	16	43	TOLERANCES UNLESS OTHERWISE SPECIFIED		
APD	8	17	53	DIMENSION	UP TO	OVER
				0.5 - 3	3 - 6	6 - 30
				TOLERANCE	±0.1	±0.1
				3RD ANGLE PROJECTION	±0.2	±0.3
				TITLE		
				JUNCTION BLOCK		
				NON-FEED - THRU		
				REVISION		
				DRWG. NO.		
				OL - JBPT5N01ZXB		