






PART NO.	MAX. CONTINUOUS OPERATING VOLTAGE (AC)	NOMINAL AC VOLTAGE	ELECTRICAL SYSTEM	REVISION			
				REV	DATE	DESCRIPTION	
				A	5/16/23	526444GCP - RELEASE MRY	
SPDN-A120-1P	180	120	SINGLE PHASE				
SPDN-A120-2S	180	240/120	SPLIT PHASE				
SPDN-A120-3Y	150	208/120	3 PHASE WYE				
SPDN-A240-1P	350	240	SINGLE PHASE				
SPDN-A240-3D	275	240	3 PHASE DELTA				
SPDN-A277-3Y	350	480/277	3 PHASE WYE				
SPDN-A480-3D	550	480	3 PHASE DELTA				




WIRING CONFIGURATION

Split




2 Hots, 1 Neu, 1 Grnd

WYE




3 Hots, 1 Neu, 1 Grnd

Delta & HRG WYE



3 Hots, 1 Grnd

Single Pole




1 Hot, 1 Neu, 1 Grnd

NOTES:

1. STANDARD LEAD LENGTH: 18-20"

2. ENCLOSURE RATING: POLYCARBONATE 4X

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			
MATL SPEC		FINISH		
DRW myork	DATE 2/28/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSTIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994				
3RD ANGLE PROJECTION				
TITLE SURGE PROTECTION DEVICE, UL TYPE 2 OUTLINE				
		REVISION A	DRWG NO. OL-SPDN-A	SHEET 1 OF 1