

# FUSES AND THE CONSTRUCTION MARKET



## Quality Products, Excellent Service, and Technical Expertise!

Littelfuse offers innovative and quality UL fuses for the commercial construction market. Our UL fuses serve numerous functions to meet your customers most stringent protection needs. Whether indicating or non-indicating, low voltage or high voltage, short circuit to overload protection, Littelfuse has a fuse to fit your application.

Class L: Current limiting protection				
KLPC Series	Time Delay	600 VAC/480 VDC	Up to 6000 Current Amperes AC/DC Rating	
KLLU Series	Time Delay	600 VAC/300 VDC	Up to 4000 Current Amperes AC/DC Rating	
LDC Series (all-purpose AC/DC)	Fast Acting	600 VAC/VDC	Up to 2000 Current Amperes AC/DC Rating	
RK1: Short circuit and overload protection				
LLSRK/LLSRK_ID Series and LLNRK Series	Time Delay	Dual Element	600 VAC/300 VDC and 250 VAC/125 VDC	Up to 600 Current Amperes AC/DC Rating
KLNR/KLSR Series	Fast Acting	250/600 VAC and 125 VDC/250 and 300 VDC	Up to 600 Current Amperes AC/DC Rating	

Our Partner:



**RK5: Short circuit and overload protection**

<b>FLNR/FLNR_ID Series</b>	Time Delay	Dual Element	250 VAC/125 VDC	Up to 600 Current Amperes AC/DC Rating
<b>FLSR/FLSR_ID Series</b>	Time Delay	Dual Element	600 VAC/300 VDC	Up to 600 Current Amperes AC/DC Rating
<b>IDSR_ID Series</b>	Time Delay	Dual Element	600 VAC/600 VDC	Up to 600 Current Amperes AC/DC Rating

**Class J: Maximum protection designed to save space**

<b>JTD/JTD_ID Series</b>	Time Delay	600 VAC/500 VDC and 600 VAC/300 VDC	Up to 600 Current Amperes AC/DC Rating
<b>JLS Series</b>	Fast Acting	600 VAC	Up to 600 Current Amperes AC Rating

**Class T: Compact size short circuit protection**

<b>JLLN Series</b>	Fast Acting	300 VAC/160 and 125 VDC	Up to 1200 Current Amperes AC/DC Rating
<b>JLLS Series</b>	Fast Acting	600 VAC/300 VDC	Up to 1200 Current Amperes AC/DC Rating

**Class CC: Small space saving protection of motor circuits**

CCMR Series	Time Delay	Dual Element	600 VAC/300 and 500 VDC	Up to 30 Current Amperes AC/DC Rating
KLDR Series	Time Delay	600 VAC/300 VDC	Up to 30 Current Amperes AC/DC Rating	
KLKR Series	Fast Acting	Dual Element	600 VAC/300 VDC	Up to 30 Current Amperes AC/DC Rating

**Class CD: Small space saving protection of motor circuits**

<b>CCMR Series</b>	Time Delay	Dual Element	600 VAC/250 VDC	Up to 60 Current Amperes AC/DC
--------------------	------------	--------------	-----------------	--------------------------------

**Midget: Supplemental overage protection for control circuits**

<b>BLF</b>	Fast Acting	250 and 125 VAC	Up to 30 Current Amperes AC
<b>BLN</b>	Fast Acting	250 VAC	Up to 30 Current Amperes AC
<b>BLS</b>	Fast Acting	600 and 250 VAC	Up to 10 Current Amperes AC
<b>FLA</b>	Time Delay	125 VAC	Up to 30 Current Amperes AC
<b>FLM</b>	Time Delay	250 VAC/125 VDC	Up to 30 Current Amperes AC/DC
<b>FLQ</b>	Time Delay	500 VAC/300 VDC	Up to 30 Current Amperes AC/DC
<b>KLK</b>	Fast Acting	600 VAC/500 VDC	Up to 30 Current Amperes AC/DC
<b>KLKD</b>	Fast Acting	600 VAC/VDC	Up to 30 Current Amperes AC/DC
<b>KLQ</b>	Time Delay	600 VAC	Up to 6 Current Amperes AC
<b>FLU</b>	Fast Acting	1000 VAC/VDC	Up to 11 Current Amperes AC/DC



To view Industrial Power and UL Fuses, please scan QR code.

- ★ 5-Star Technical Application Assistance
- 📞 1-800-TEC-FUSE
- ✉ techline@littelfuse.com

Disclaimer Notice—Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/product-disclaimer](http://www.littelfuse.com/product-disclaimer).