


# AQ1250-01ETG

## 50A Discrete Unidirectional TVS Diode, General Purpose Surge Protection



**Note:** This package image is for example and reference only. For detail package drawing, please refer to the package section in this datasheet.

### Pinout



### Functional Block Diagram



### Description

The AQ1250-01ETG unidirectional TVS is fabricated in a proprietary silicon avalanche technology. These diodes provide a high ESD (electrostatic discharge) protection level for electronic equipment. The AQ1250 TVS can safely absorb repetitive ESD strikes of  $\pm 30$  kV (contact and air discharge as defined in IEC 61000-4-2) without any performance degradation. Additionally, each TVS can safely dissipate a 50A 8/20 $\mu$ s surge event as defined in IEC 61000-4-5 2<sup>nd</sup> edition.

### Features

- ESD, IEC 61000-4-2,  $\pm 30$ kV contact,  $\pm 30$ kV air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Lightning, 50A (8/20 $\mu$ s as defined in IEC 61000-4-5 2<sup>nd</sup> edition)
- ESD, ISO 10605, 330pF 330 $\Omega$ ,  $\pm 30$ kV contact,  $\pm 30$ kV air
- Low leakage current of 0.02 $\mu$ A (TYP) at 5V
- Halogen free, lead free and RoHS compliant
- Moisture Sensitivity Level 1
- AEC-Q101 qualified and PPAP capable

### Applications

- Switches / Buttons
- Test Equipment / Instrumentation
- Medical Equipment
- Battery
- Automotive applications

#### Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications  
The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

**AQ1250-01ETG****50A Discrete Unidirectional TVS Diode, General Purpose Surge Protection****Absolute Maximum Ratings**

Symbol	Parameter	Value	Units
$I_{PP}$	Peak Current ( $t_p=8/20\mu s$ )	50	A
$T_{OP}$	Operating Temperature	-40 to 150	°C
$T_{STOR}$	Storage Temperature	-55 to 150	°C



**Caution:** Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

**Electrical Characteristics ( $T_{OP}=25^\circ C$ )**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	$V_{RWM}$	$I_R=1\mu A$			5	V
Breakdown Voltage	$V_{BR}$	$I_R=1mA$	5.2	5.5		V
Reverse Leakage Current	$I_{LEAK}$	$V_R=5V$		0.02	0.1	$\mu A$
Clamp Voltage <sup>1</sup>	$V_C$	$I_{PP}=50A, t_p=8/20\mu s$		8.7	10	V
Dynamic Resistance <sup>2</sup>	$R_{DYN}$	TLP, $t_p=100ns$		0.05		$\Omega$
ESD Withstand Voltage <sup>1</sup>	$V_{ESD}$	IEC 61000-4-2 (Contact Discharge)	$\pm 30$			kV
		IEC 61000-4-2 (Air Discharge)	$\pm 30$			kV
Diode Capacitance <sup>1</sup>	$C_{IO-GND}$	Reverse Bias=0V, $f=1MHz$		120		pF

**Note:**


- Parameter is guaranteed by design and/or component characterization.
- Transmission Line Pulse (TLP) with 100ns width, 0.2ns rise time, and average window  $t_1=70ns$  to  $t_2=90ns$

**Capacitance vs Reverse Bias****Clamping Voltage vs  $I_{PP}$** 


# AQ1250-01ETG

50A Discrete Unidirectional TVS Diode, General Purpose Surge Protection


Positive Transmission Line Pulsing (TLP) Plot




Negative Transmission Line Pulsing (TLP) Plot




IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage




IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage



ISO10605 contact discharge plot at +8 kV




ISO10605 contact discharge plot at -8 kV



# AQ1250-01ETG


## 50A Discrete Unidirectional TVS Diode, General Purpose Surge Protection

### 8/20μs Pulse Waveform



### Soldering Parameters

<b>Reflow Condition</b>		Pb – Free assembly
<b>Pre Heat</b>	- Temperature Min ( $T_{s(min)}$ )	150°C
	- Temperature Max ( $T_{s(max)}$ )	200°C
	- Time (min to max) ( $t_s$ )	60 – 180 secs
<b>Average ramp up rate (Liquidus) Temp (<math>T_L</math>) to peak</b>		3°C/second max
<b><math>T_{s(max)}</math> to <math>T_L</math> - Ramp-up Rate</b>		3°C/second max
<b>Reflow</b>	- Temperature ( $T_L$ ) (Liquidus)	217°C
	- Temperature ( $t_L$ )	60 – 150 seconds
<b>Peak Temperature (<math>T_p</math>)</b>		260 <sup>+0/-5</sup> °C
<b>Time within 5°C of actual peak Temperature (<math>t_p</math>)</b>		20 – 40 seconds
<b>Ramp-down Rate</b>		6°C/second max
<b>Time 25°C to peak Temperature (<math>T_p</math>)</b>		8 minutes Max.
<b>Do not exceed</b>		260°C




### Ordering Information

Part Number	Package	Min. Order Qty.
AQ1250-01ETG	SOD882	10,000


### Product Characteristics




<b>Lead Plating</b>	Matte Tin
<b>Lead material</b>	Copper Alloy
<b>Substrate Material</b>	Silicon
<b>Body Material</b>	Molded Compound
<b>Flammability</b>	UL Recognized compound meeting flammability rating V-0

### Part Marking System



### Part Numbering System




**AQ1250-01ETG****50A Discrete Unidirectional TVS Diode, General Purpose Surge Protection****Package Dimensions — SOD882**

Recommended Soldering Pattern



Drawing#: E03-B

Symbol	SOD882					
	Millimeters			Inches		
	Min	Typ	Max	Min	Typ	Max
<b>A</b>	0.40	0.50	0.55	0.016	0.020	0.022
<b>A1</b>	0.00	0.02	0.05	0.000	0.001	0.002
<b>L1</b>	0.20	0.25	0.30	0.008	0.010	0.012
<b>L2</b>	0.45	0.50	0.55	0.018	0.020	0.022
<b>D</b>	0.95	1.00	1.05	0.037	0.039	0.041
<b>E</b>	0.55	0.60	0.65	0.022	0.024	0.026
<b>e</b>	0.65 BSC			0.026 BSC		

**Embossed Carrier Tape & Reel Specification — SOD882**

Symbol	Millimeters
<b>A0</b>	0.70+/-0.045
<b>B0</b>	1.10+/-0.045
<b>K0</b>	0.65+/-0.045
<b>F</b>	3.50+/-0.05
<b>P1</b>	2.00+/-0.10
<b>W</b>	8.00 + 0.30 -0.10

Component Orientation in Tape



**Product Disclaimer:** Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <http://www.littelfuse.com/disclaimer-electronics>