


LX8 Series

EV Series 0.8 A Sensitive TRIACs



Description:


The LX8 is a solid state switch series offering direct interface to microprocessor drivers in economical TO-92 and surface mount packages. The die voltage blocking junctions are glass-passivated to ensure long term reliability and parametric stability.

Features:


- RoHS compliant and halogen-free
- Blocking voltage (V_{DRM}) capability up to 600 V
- Surge capability > 9.5 A
- Static dv/dt > 10 V/μsec
- Thru hole and surface mount packages

Pinout Diagram



SOT-89



SOT-223



TO-92



MT1: Main Terminal 1; **MT2:** Main Terminal 2; **G:** Gate

Applications:

The LX8 EV Series is especially designed for low current applications such as heating controls in hair care products, as well as replacement of mechanical switch contacts where long life is required.

Product Summary

Symbol	Value	Unit
$I_{T(RMS)}$	0.8	A
V_{DRM}/V_{RRM}	400 to 600	V
I_{GT}	3 to 5	mA

LX8 Series

EV Series 0.8 A Sensitive TRIACs

Absolute Maximum Ratings

Symbol	Parameter			Value	Unit
$I_{T(RMS)}$	RMS on-state current (full sine wave)	TO-92	$T_c = 50^{\circ}\text{C}$	0.8	A
		SOT-89	$T_c = 60^{\circ}\text{C}$		
		SOT-223	$T_L = 90^{\circ}\text{C}$		
I_{TSM}	Non repetitive surge peak on-state current (Single cycle, T_{VJ} initial = 25°C)	-	$f = 50\text{ Hz}$	8.0	A
		-	$f = 60\text{ Hz}$	9.5	
I^2t	I^2t Value for fusing	$t_p = 10\text{ ms}$	$f = 50\text{ Hz}$	0.32	A^2s
		$t_p = 8.3\text{ ms}$	$f = 60\text{ Hz}$	0.37	
di/dt	Critical rate of rise of on-state current $I_G = 2 \times I_{GT}$		$T_{VJ} = 110^{\circ}\text{C}$	20	$\text{A}/\mu\text{s}$
I_{GTM}	Peak gate current	$t_p = 10\text{ }\mu\text{s}$	$T_{VJ} = 110^{\circ}\text{C}$	1	A
$P_{G(AV)}$	Average gate power dissipation		$T_{VJ} = 110^{\circ}\text{C}$	0.1	W
T_{stg}	Storage temperature range			-40 to 150	$^{\circ}\text{C}$
T_{VJ}	Operating junction temperature range			-40 to 110	$^{\circ}\text{C}$

Electrical Characteristics ($T_{VJ} = 25^\circ\text{C}$, unless otherwise specified)

Symbol	Description	Test Conditions	Quadrant	Limit	Value		Unit
					LX803xy	LX807xy	
I_{GT}	DC Gate Trigger Current	$V_D = 12\text{ V}$ $R_L = 60\text{ }\Omega$	I – II – III	MAX.	3	5	mA
V_{GT}	DC Gate Trigger Voltage		IV	MAX.	5	7	V
I_H	Holding Current	Gate Open	ALL	MAX.	1.3	1.3	V
dv/dt	Critical Rate-of-Rise of Off-State Voltage	$T_J = 110^\circ\text{C}$, $V_D = V_{DRM}$ Exponential Waveform Gate Open		MAX.	5	5	mA
$(dv/dt)_c$	Critical Rate-of-Rise of Commutating Voltage	$(di/dt)_c = 0.43\text{ A/ms}$ $T_{VJ} = 110^\circ\text{C}$		MIN.	10	10	$\text{V}/\mu\text{s}$
t_{gt}	Turn-On Time	$I_G = 25\text{ mA}$ $P_W = 15\text{ }\mu\text{s}$ $I_T = 1.2\text{ A (pk)}$		MIN.	1.5	1.5	$\text{V}/\mu\text{s}$
				MAX.	2.0	2.0	μs

Note: x = voltage, y = package

Static Characteristics ($T_{VJ} = 25^\circ\text{C}$, unless otherwise specified)

Symbol	Description	Test Conditions	Limit	Value	Unit
V_{TM}	Peak On-State Voltage	$I_{TM} = 1.13\text{ A (pk)}$	MAX	1.60	V
I_{DRM}	Off-State Current, Peak Repetitive	$V_D = V_{DRM}$ $T_{VJ} = 25^\circ\text{C}$	MAX	5	μA
		$V_D = V_{DRM}$ $T_{VJ} = 110^\circ\text{C}$		100	μA

Thermal Characteristics

Symbol	Description	Test Conditions	Value	Unit
R_{thJC}	Junction to case (AC)	$I_T = 0.8\text{ A}_{(RMS)}$ ¹	TO-92	K/W
			SOT-89	
			SOT-223	
R_{thJA}	Junction to ambient	$I_T = 0.8\text{ A}_{(RMS)}$ ¹	TO-92	K/W
			SOT-89	
			SOT-223	

1. 60 Hz AC resistive load condition, 100% conduction

LX8 Series

EV Series 0.8 A Sensitive TRIACs

Figure 1: Definition of Quadrants




Figure 2: Normalized DC Gate Trigger Current for All Quadrants vs. Junction Temperature




Figure 3: Normalized DC Holding Current vs. Junction Temperature




Figure 4: Normalized DC Gate Trigger Voltage for All Quadrants vs. Junction Temperature




Figure 5: Power Dissipation (Typical) vs. RMS On-State Current






Figure 6: Maximum Allowable Case Temperature vs. On-State Current



LX8 Series


EV Series 0.8 A Sensitive TRIACs

Figure 7: Surge Peak On-State Current vs. Number of Cycles



Soldering Parameters

Reflow Condition		Pb-free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 180 secs
Average ramp up rate (Liquidus Temp) (T_L) to peak		5°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		5°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Time (min to max) (t_s)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		20 – 40 seconds
Ramp-down Rate		5°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		280°C



LX8 Series

EV Series 0.8 A Sensitive TRIACs


Physical Specifications

Terminal Finish	100% Matte Tin-plated.
Body Material	UL Recognized compound meeting flammability rating V-0.
Lead Material	Copper Alloy

Design Considerations

Careful selection of the correct component for the application's operating parameters and environment will go a long way toward extending the operating life of the Thyristor. Good design practice should limit the maximum continuous current through the main terminals to 75% of the component rating. Other ways to ensure long life for a power discrete semiconductor are proper heat sinking and selection of voltage ratings for worst case conditions. Overheating, overvoltage (including dv/dt), and surge currents are the main killers of semiconductors. Correct mounting, soldering, and forming of the leads also help protect against component damage.

Dimensions — TO-92 (E Package)



Reliability/Environmental Tests


Test	Specifications and Conditions
AC Blocking	MIL-STD-750, M-1040, Cond A Applied Peak AC voltage @ 110°C for 1008 hours
Temperature Cycling	MIL-STD-750, M-1051, 100 cycles; -40°C to +150°C; 15-min dwell-time
Temperature/Humidity	EIA / JEDEC, JESD22-A101 1008 hours; 320 V - DC: 85°C; 85% rel humidity
High Temp Storage	MIL-STD-750, M-103, 1008 hours; 150°C
Low-Temp Storage	1008 hours; -40°C
Resistance to Solder Heat	MIL-STD-750 Method 2031
Solderability	ANSI/J-STD-002, category 3, Test A
Lead Bend	MIL-STD-750, M-2036 Cond E

Dimensions	Inches		Millimeters	
	Min	Max	Min	Max
A	0.175	0.205	4.450	5.200
B	0.170	0.210	4.320	5.330
C	0.500	-	12.70	-
D	0.135	-	3.430	-
E	0.125	0.165	3.180	4.190
F	0.080	0.105	2.040	2.660
G	0.016	0.021	0.407	0.533
H	0.045	0.055	1.150	1.390
I	0.095	0.105	2.420	2.660
J	0.015	0.020	0.380	0.500


LX8 Series

EV Series 0.8 A Sensitive TRIACs

Dimensions – SOT-89




Pad Layout for SOT-89




Dimensions in Millimeters (Inches)

Dimension	Inches			Millimeters		
	Min	Typ	Max	Min	Typ	Max
A	0.173	—	0.181	4.40	—	4.60
B	0.090	—	0.102	2.29	—	2.60
C	0.055	—	0.063	1.40	—	1.60
D	0.155	—	0.167	3.94	—	4.25
E	0.032	—	0.047	0.81	—	1.20
F	—	0.059	—	—	1.5	—
G	—	0.118	—	—	3	—
H	0.014	—	0.017	0.35	—	0.44
I	0.014	—	0.019	0.36	—	0.48
J	—	0.065	—	—	1.65	—

Dimensions – SOT-223



Pad Layout for SOT-223



Dimensions in Millimeters (Inches)

Dimensions	Inches			Millimeters		
	Min	Typ	Max	Min	Typ	Max
A	0.248	0.256	0.264	6.30	6.50	6.70
B	0.130	0.138	0.146	3.30	3.50	3.70
C	—	—	0.071	—	—	1.80
D	0.001	—	0.004	0.02	—	0.10
E	0.114	0.118	0.124	2.90	3.00	3.15
F	0.024	0.027	0.034	0.60	0.70	0.85
G	—	0.090	—	—	2.30	—
H	—	0.181	—	—	4.60	—
I	0.264	0.276	0.287	6.70	7.00	7.30
J	0.009	0.010	0.014	0.24	0.26	0.35
K	10° MAX					

LX8 Series

EV Series 0.8 A Sensitive TRIACs

Product Selector


Part Number	Voltage	Gate Sensitivity Quadrants		Package
		I – II – III	IV	
LX803DE	400 V	3 mA	5 mA	TO-92
LX803ME	600 V	3 mA	5 mA	TO-92
LX803DT	400 V	3 mA	5 mA	SOT-223
LX803MT	600 V	3 mA	5 mA	SOT-223
LX807DE	400 V	5 mA	7 mA	TO-92
LX807ME	600 V	5 mA	7 mA	TO-92
LX807DT	400 V	5 mA	7 mA	SOT-223
LX807MT	600 V	5 mA	7 mA	SOT-223
LX807MB	600 V	5 mA	7 mA	SOT-89

Packing Options


Part Number	Marking	Weight	Packing Mode	Base Quantity
LX8xxyE	LX8xxyE	0.217 g	Bulk	2500
LX8xxyEAP	LX8xxyE	0.217 g	Ammo Pack	2000
LX8xxyERP	LX8xxyE	0.217 g	Tape & Reel	2000
LX8xxyTRP	LX8xxyT	0.120 g	Tape & Reel	1000
LX8xxyBRP	8xx	0.053 g	Tape & Reel	1000

Note: xx = gate sensitivity, y = voltage

Part Numbering System



Part Marking System




LX8 Series

EV Series 0.8 A Sensitive TRIACs


TO-92 (3-lead) Reel Pack (RP) Radial Led Specifications

Meets all EIA-468-C Standards



TO-92 (3-lead) Ammo Pack (AP) Radial Led Specifications


Meets all EIA-468-C Standards




LX8 Series

EV Series 0.8 A Sensitive TRIACs

SOT-89 Reel Pack (RP) Specifications




SOT-89 Reel Pack (RP1) Specifications



LX8 Series

EV Series 0.8 A Sensitive TRIACs

SOT-223 Reel Pack (RP) Specifications



Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.

Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

