



- NOTES:
 1). RATING: NO: 14Vdc/20A
 2). TEMPERATURE RANGE: -40C TO 125C
 3). RELAY IS FLUX-TIGHT.
 4). ALL DIMENSIONS SHOWN FOR REFERENCE ONLY.

METRIC COMPONENT

| NO | COMPONENT NO | DESCRIPTION | QTY/M | U/M |
|---|---|-------------|-------|-----|
| BILL OF MATERIAL | | | | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING. | | | | |
| ⊙ | DENOTES CRITICAL CHARACTERISTICS. | | | |
| CPK | DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE | | | |
| (ST) | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS | | | |
| CP | DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE | | | |

| COPIES TO | | MATERIAL SPEC | |
|--|-----------|-----------------------|-----------|
| 1 | 9 | 18 | FINISH |
| 2 | 10 | 19 | |
| 3 | 12 | 20 | |
| 4 | 13 | 21 | DRW CAD |
| 5 | 14 | 23 | CHK |
| 6 | 15 | 33 | DATE |
| 7 | 16 | 43 | APPD |
| 8 | 17 | 53 | DATE |
| TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-PM) | | | |
| DIMENSION | 0.5 - 1.5 | 1.5 - 5.0 | 5.0 - 120 |
| TOLERANCE | ±0.10 | ±0.05 | ±0.1 |
| 3RD ANGLE PROJECTION | | | |
| TITLE SINGLE POLE, NORMALLY OPEN | | | |
| MINI-MICRO RELAY | | | |
| REVISION DRWG. NO. | | | |
| B 02040080Z | | | |
| GRAMS/PIECE | | | |
| 30 ^{0.0} - 50 ^{0.0} ±0.15 | | | |
| 120 ^{0.0} - 400 ^{0.0} ±0.2 | | | |
| LTR | DATE | REVISION | CHK |
| A | 06/24/09 | 000716ER RELEASED | CAD |
| B | 08/08/11 | 503010ERA-SEE ERN GMB | |

