



THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	C	ECN #07221: NOTES	6/21/07	
	D	ECN #08037: NOTE5: BAGGED HARDWARE	1/16/08	
	E	ECO #521466: UPDATED NOTES, ADDED ITEM 1 AND 2 COLUMNS TO TABLE, UPDATED GEOMETRY	6/30/20	T.SURMA



46377-10 SHOWN



mm [inch]

- (E) NOTES:
- MATERIAL: BLACK THERMOPLASTIC
 - ACCEPTS ATC AND ATO TYPE FUSES AND PLUG-IN TYPE CIRCUIT BREAKERS
 - .250" x .032" QUICK CONNECT TERMINALS, TIN PLATED COPPER; 22.5A MAX PER CIRCUIT @12VDC; FOR 24VDC APPLICATIONS, USE 24VDC RATED FUSES AND BREAKERS ONLY.
 - INPUT STUD #10-32: 100A MAX FOR INPUT STUD, TORQUE, 2.25N-m(20 in-lbs) MAX
 - MOUNTING HOLE TORQUE: 0.9N-m (8 in-lbs) MAX.
 - INPUT WIRE SIZE: #4-6 AWG.
 - OUTPUT WIRE SIZE: #12-16 AWG.
 - ALL DIMENSIONS ARE REFERENCE.
 - HARDWARE BAGGED.

46377-20(OBSOLETE)(E)	20	173.74 [6.84]	127.0 [5.00]	46376-20	47105-11
46377-18	18	157.99 [6.22]	111.00 [4.37]	46376-18	47105-11
46377-14(OBSOLETE)(E)	14	126.24 [4.97]	79.25 [3.12]	46376-14	47105-11
46377-12	12	110.24 [4.34]	63.50 [2.50]	46376-12	47105-11
46377-10	10	95.25 [3.75]	47.62 [1.87]	46376-10	47105-11
46377-8	8	78.48 [3.09]	31.75 [1.25]	46376-8	47105-11
46377-6	6	62.74 [2.47]	15.85 [0.62]	46376-6	47105-11
PART NO.	POS.	A DIM.	B DIM.	ITEM 1	ITEM 2

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

●	FIT/ FUNCTION CRITICAL CHARACTERISTICS
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF.ISO2768-M) FOR METAL, REF SPI PLASTICS

DIMENSION MM	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400	ANGLE
TOLERANCES	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5°

NAME	DATE
DRAWN MJT	8/19/91
CHECKED -	-
-	-
-	-

FORM NO: CVP-PE40-0003 REV A

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

Littelfuse
Expertise Applied | Answers Delivered

TITLE: FUSE BLOCK

SIZE B DWG. NO. 46377, CHART REV. E

SCALE 1:2 SHEET 1 OF 1