



METRIC
COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

LTR	DATE	REVISION	CHK	APD
A	06/21/16	516036GCA- INITIAL RELEASE FYUE		

COPIES TO	MATL SPEC	2.0mm MS PLATE
1 9 18	FINISH	ZINC CHROMATE PLATED (t = 3-8 microns)
2 10 19	DRW	FYUE
3 12 20	CHK	DATE 21/Jun/16
4 13 21	DATE	SCALE 1:1
5 14 23	DATE	SUPER DR
6 15 33	DATE	FINISH GOOD WT
7 16 43	DATE	GRAMS/PIECE
8 17 53	DATE	

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)	UP TO 0.5	UP TO 3	UP TO 6	UP TO 30	UP TO 120	UP TO 400
DIMENSION	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5
TOLERANCE						

3RD ANGLE PROJECTION

TITLE METAL BRACKET (for HWB18)

REVISION DRWG. NO. 868-066

OUTLINE

Littelfuse
LIPA CITY, BATANGAS, PHILIPPINES