



NOTES:  
 1. MATERIAL: COPPER C1100, TIN PLATED  
 2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION  
 3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.  
 DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

◎	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
⊠	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

COPIES TO		MATERIAL SPECIFICATION	
LTR	DATE	REVISED BY	DATE
A	06/26/13	508674ERA-RELEASE	FYUE
B	07/10/13	508881ECA-THICKNESS 2.3 WAS 2.0	FYUE

NO		COMPONENT NO		DESCRIPTION		QTY/M		U/M	
BILL OF MATERIAL									
MATERIAL SPECIFICATION					SEE NOTE				
FINISH					SEE NOTE				
DRW	FYUE	DATE	06/26/13	SCALE	2:1				
CHK		DATE		SUPER DR					
APPD		DATE		FINISH GOOD WT	GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)									
DIMENSION	0.5 - 3	UP TO OVER	UP TO OVER	UP TO OVER	UP TO OVER	UP TO OVER	UP TO OVER	UP TO OVER	UP TO OVER
TOLERANCE	+0.05	+0.05	+0.1	+0.15	+0.15	+0.2	+0.2	+0.2	+0.2
3RD ANGLE PROJECTION									
TITLE 2 POSITION BUS BAR - FLEX MIDI HOLDER									
LITTELFUSE					REVISION DRWG. NO.				
CHICAGO, USA 773-628-1000					B OL-882-267-002				