



- NOTES:
 1. MATERIAL: COPPER C1100, TIN PLATED
 2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION
 3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD																																																																						
A	06/26/13	50B674ERA-RELEASE FYUE																																																																								
B	07/10/13	50B881ECA-THICKNESS 2.3 WAS 2.0 FYUE																																																																								
<table border="1"> <tr> <td>COPIES TO</td> <td colspan="4">MATL SPEC</td> </tr> <tr> <td>1 9 18</td> <td colspan="4">SEE NOTE</td> </tr> <tr> <td>2 10 19</td> <td colspan="4">FINISH</td> </tr> <tr> <td>3 12 20</td> <td colspan="4">SEE NOTE</td> </tr> <tr> <td>4 13 21</td> <td>DATE</td> <td>06/26/13</td> <td>SCALE</td> <td>2:1</td> </tr> <tr> <td>5 14 23</td> <td>DATE</td> <td></td> <td>SUPER DR</td> <td></td> </tr> <tr> <td>6 15 33</td> <td>DATE</td> <td></td> <td>FINISH GOOD WT</td> <td>GRAMS/PIECE</td> </tr> <tr> <td>7 16 43</td> <td>DATE</td> <td></td> <td></td> <td></td> </tr> <tr> <td>8 17 53</td> <td colspan="4">TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)</td> </tr> <tr> <td>DIMENSION</td> <td>0.5 - 3</td> <td>UP TO OVER</td> <td>UP TO OVER</td> <td>UP TO OVER</td> </tr> <tr> <td>TOLERANCE</td> <td>+0.05</td> <td>+0.05</td> <td>+0.1</td> <td>+0.15</td> </tr> <tr> <td>3RD ANGLE PROJECTION</td> <td colspan="4"> TITLE 3 POSITION BUS BAR - FLEX MIDI HOLDER </td> </tr> <tr> <td colspan="3"> CHICAGO, USA 773-628-1000 </td> <td>REVISION</td> <td>DRWG. NO.</td> </tr> <tr> <td colspan="3"></td> <td>B</td> <td>OL-882-267-003</td> </tr> </table>					COPIES TO	MATL SPEC				1 9 18	SEE NOTE				2 10 19	FINISH				3 12 20	SEE NOTE				4 13 21	DATE	06/26/13	SCALE	2:1	5 14 23	DATE		SUPER DR		6 15 33	DATE		FINISH GOOD WT	GRAMS/PIECE	7 16 43	DATE				8 17 53	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)				DIMENSION	0.5 - 3	UP TO OVER	UP TO OVER	UP TO OVER	TOLERANCE	+0.05	+0.05	+0.1	+0.15	3RD ANGLE PROJECTION	TITLE 3 POSITION BUS BAR - FLEX MIDI HOLDER				CHICAGO, USA 773-628-1000			REVISION	DRWG. NO.				B	OL-882-267-003
COPIES TO	MATL SPEC																																																																									
1 9 18	SEE NOTE																																																																									
2 10 19	FINISH																																																																									
3 12 20	SEE NOTE																																																																									
4 13 21	DATE	06/26/13	SCALE	2:1																																																																						
5 14 23	DATE		SUPER DR																																																																							
6 15 33	DATE		FINISH GOOD WT	GRAMS/PIECE																																																																						
7 16 43	DATE																																																																									
8 17 53	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)																																																																									
DIMENSION	0.5 - 3	UP TO OVER	UP TO OVER	UP TO OVER																																																																						
TOLERANCE	+0.05	+0.05	+0.1	+0.15																																																																						
3RD ANGLE PROJECTION	TITLE 3 POSITION BUS BAR - FLEX MIDI HOLDER																																																																									
CHICAGO, USA 773-628-1000			REVISION	DRWG. NO.																																																																						
			B	OL-882-267-003																																																																						