



NOTE:

1. MATERIAL: 30 DURO SILICONE (GREEN)
2. OPERATING & STORAGE TEMPERATURE: -40 °C TO 85 °C
3. ALL DIMENSIONS SHOWN FOR REFERENCE ONLY
4. USED ON HWB18 BASE (#868-063)
5. GASKET MUST BE FULLY SEATED IN CHANNEL OF HWB18 BASE TO MAINTAIN SEALING

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙		DENOTES CRITICAL CHARACTERISTICS.		
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		

LTR	DATE	REVISION	CHK	APD
A	04/01/12	504798ERA - INITIAL RELEASE FYUE		
B	05/18/12	504988ECA - ADDED ERN NUMBER TO REVISION A FYUE		

COPIES TO	MATL SPEC				REFER TO NOTE 1			
1 9 18	FINISH							
2 10 19	DRW	FYUE	DATE	04/01/12	SCALE	2:1		
3 12 20	CHK		DATE		SUPER DR			
4 13 21	APPD		DATE		FINISH GOOD WT	GRAMS/PIECE		
5 14 23	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)							
6 15 33	DIMENSION	0.5 - 3	UP TO	3 - 6	UP TO	6 - 30	UP TO	30 - 120
7 16 43	TOLERANCE	±0.05	UP TO	±0.05	UP TO	±0.1	UP TO	±0.15
8 17 53	3RD ANGLE PROJECTION							
TITLE					RUBBER SEAL OUTLINE (HWB18)			
REVISION					DRWG. NO.			
B					OL-901-106			

