





LTR	DATE	REVISION	CHK	APD
A	19/Sep/16	516415GCC-NEW RELEASE FYUE		



NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO	MATL SPEC			
1 9 18	FINISH			
2 10 19				
3 12 20				
4 13 21	DRW	FYUE	DATE	06/06/14
5 14 23	CHK		DATE	
6 15 33	APPD		DATE	
7 16 43				FINSH GOOD WT
8 17 53				GRAMS/PIECE
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)				
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE	+0.1	+0.1	+0.2	+0.3
3RD ANGLE PROJECTION	TITLE GRID			
METRIC COMPONENT		Littelfuse		CHICAGO, USA 773-628-1000
REVISION	DRWG. NO.			
A	OL-901-322			

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)