



- NOTES:
 1). RATING: NO: 14Vdc/35A
 NC: 14Vdc/20A
 2). TEMPERATURE RANGE: -40C TO 125C
 3). RELAY IS FLUX-TIGHT.
 4). ALL DIMENSIONS SHOWN FOR REFERENCE ONLY.

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

COPIES TO		MATL SPEC	
1	9	18	FINISH
2	10	19	DRW
3	12	20	CAD
4	13	21	CHK
5	14	23	APPD
6	15	33	SCALE
7	16	43	DATE
8	17	53	DATE

LTR	DATE	REVISION	CHK	APD
A	06/24/09	000716ER RELEASED	CAD	
B	08/08/11	503010ERA-SEE ERN GMB		
C	04/18/12	504753ECA ADD DIODE VERSION EJIN		

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)	UP TO	OVER	UP TO	OVER	UP TO	OVER	UP TO	OVER	UP TO	OVER
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400					
TOLERANCE	±0.05	±0.05	±0.1	±0.15	±0.2					

TITLE		SINGLE POLE, DOUBLE THROW	
MICRO RELAY		GRAMS/PIECE	
3RD ANGLE PROJECTION		FINISH GOOD WT	
REVISION		SCALE	
C		2:1	
DRWG. NO.		SUPER DR	
02040090Z		DATE	
		DATE	
		DATE	

