



NOTES:

1. THIS RETAINER IS SUPPLIED WITH THREE (3) SPRINGS, MAKING IT SUITABLE FOR 9, 14 + 20 AMP "SFE" FUSES BY SELECTING THE PROPER SPRING.
2. FOR PANEL MOUNTING OF THIS RETAINER, ORDER SPRING CLIP -900-028.
3. SPRINGS MAY BE SHIPPED ASSEMBLED EITHER INSIDE OR OUTSIDE OF FUSEHOLDER BODY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE 1.0
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. REFERENCE PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC IS LOCATED IN THE DRAWING INSTRUCTION.
 DIMENSIONS CP DIMENSIONS.-MINIMUM CP VALUE SHALL BE WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE DRAWING INSTRUCTION FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC	FINISH	
1	9	DRW	JMB	DATE 1/12/98 SCALE 1=1
2	10	19	CHK	DATE SUPER DRW
3	12	20	4	13 21
4	13	21	APPD	DATE RAW STK WT
5	14	23	6	15 33
6	15	33	7	16 43
7	16	43	8	17 53
8	17	53	TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC ±.01 FRACTION ± THREE PLACE DEC ±.005 ANGULAR ±1°	
TITLE				
IN-LINE BAYONET KNOB FUSEHOLDER				
LTR		REVISION		CHK APD
C	38958C-	REVISED & REDRAWN ON NEW FORMAT	JMB	

Littelfuse
 DES PLAINES, ILLINOIS 60016
 DRAWING NO. OFHP0001Z
 C