



NOTES:

1. THIS RETAINER IS SUPPLIED WITH THREE (3) SPRINGS, MAKING IT SUITABLE FOR 9, 14 + 20 AMP "SFE" FUSES BY SELECTING THE PROPER SPRING.
2. FOR PANEL MOUNTING OF THIS RETAINER, ORDER SPRING CLIP -900-028.
3. SPRINGS MAY BE SHIPPED ASSEMBLED EITHER INSIDE OR OUTSIDE OF FUSEHOLDER BODY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

NOTES CRITICAL CHARACTERISTICS.

MINIMUM CPK VALUE 1.0

NOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. THE PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC IS LOCATED IN THE APPROPRIATE LITTELFUSE INSPECTION INSTRUCTIONS.

MINIMUM CP VALUE 0.15 WITHIN THE DIMENSIONAL LIMITATIONS AND WITHIN THE DIMENSIONAL LIMITATIONS LOCATED TO THE DRAWING FOR MAXIMUM TOOL LIFE.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		FINISH		
1	9	DRW	JMB	DATE 1/12/98 SCALE 1=1
2	10	19	CHK	DATE SUPER DRW
3	12	20		DATE
4	13	21	APPD	DATE RAW STK WT
5	14	23		
6	15	33		LBS/M
7	16	43		TOLERANCE UNLESS OTHERWISE SPECIFIED
8	17	53		TWO PLACE DEC ± FRACTION ± ANGULAR ±1°
TITLE		IN-LINE BAYONET KNOB FUSEHOLDER		

LTR	REVISION	CHK	APD
C	38958C- REVISED & REDRAWN ON NEW FORMAT	JMB	



 DES PLAINES, ILLINOIS 60016

DRAWING NO. OFHP0001Z
 OUTLINE

UNCONTROLLED DOCUMENT