

58312-RR2 ⓑ	SPDT	ON 2 & 1	NONE	ON 2 & 3	BLACK	1,2,3 & 4					L	RED	RED	12VDC L.E.D	12VDC L.E.D	4	
58312-RG2 ⓑ	SPDT	ON 2 & 1	NONE	ON 2 & 3	BLACK	1,2,3 & 4					L	RED	GREEN	12VDC L.E.D	12VDC L.E.D	4	
58312-AR2 ⓑ	SPDT	ON 2 & 1	NONE	ON 2 & 3	BLACK	1,2,3 & 4					L	RED	GREEN	12VDC L.E.D	12VDC L.E.D	4	
58312-RG1 ⓑ	SPDT	ON 2 & 1	OFF	ON 2 & 3	BLACK	1,2,3 & 5					L	RED	GREEN	12VDC L.E.D	12VDC L.E.D	6	YES
58312-AR1 ⓑ	SPDT	ON 2 & 1	OFF	ON 2 & 3	BLACK	1,2,3 & 5					L	AMBER	RED	12VDC L.E.D	12VDC L.E.D	6	YES
58312-RR	SPDT	ON 2 & 1	OFF	ON 2 & 3	BLACK	1,2,3 & 4					L	RED	RED	12VDC L.E.D	12VDC L.E.D	4	
58312-RC	SPDT	ON 2 & 1	OFF	ON 2 & 3	BLACK	1,2,3 & 4					L	RED	CLEAR	12VDC L.E.D	12VDC L.E.D	4	
58312-RG	SPDT	ON 2 & 1	OFF	ON 2 & 3	BLACK	1,2,3 & 4					L	RED	GREEN	12VDC L.E.D	12VDC L.E.D	4	
58312-AR	SPDT	ON 2 & 1	OFF	ON 2 & 3	BLACK	1,2,3 & 4					L	AMBER	RED	12VDC L.E.D	12VDC L.E.D	4	
58312-AG	SPDT	ON 2 & 1	OFF	ON 2 & 3	BLACK	1,2,3 & 4					L	AMBER	GREEN	12VDC L.E.D	12VDC L.E.D	4	
58312-A5 ⓑ	SPST	OFF	NONE	ON 2 & 3	BLACK	2,3 & 4	Ⓟ		D	WHITE	K	AMBER		12VDC L.E.D		1	
58312-R4	SPST	OFF	NONE	ON 2 & 3	BLACK	2,3 & 4					K	RED		12VDC L.E.D		1	
58312-G4	SPST	OFF	NONE	ON 2 & 3	BLACK	2,3 & 4					K	GREEN		12VDC L.E.D		1	
58312-C4	SPST	OFF	NONE	ON 2 & 3	BLACK	2,3 & 4					K	CLEAR		12VDC L.E.D		1	
58312-B4	SPST	OFF	NONE	ON 2 & 3	BLACK	2,3 & 4					K	BLUE		12VDC L.E.D		1	
58312-A4	SPST	OFF	NONE	ON 2 & 3	BLACK	2,3 & 4					K	AMBER		12VDC L.E.D		1	
PT NO	TYPE OF SW	POS A	POS B	POS C	ROCKER COLOR	TERMINAL LOCATION	IMPRINT #1	IMPRINT #2	IMPRINT LOCATION	IMPRINT COLOR	LENS LOCATION	LENS 1	LENS 2	LENS 1	LENS 2	LAMP SCHEM	BUS BARS
		ROCKER POSITION										LENS COLOR		LAMP VOLTAGE			

**Tolerances** Unless otherwise specifically noted, the following are default tolerances:  
 \* 2-place Decimal Dimensions +/- .02"  
 \* 3-place Decimal Dimensions +/- .005"  
 \* Angular Dimensions +/- 1.0 Deg.  
 \* Metric: Refer to equivalent English Dimension Tolerance  
 >>> NOTE: All tolerances are Non-Cumulative. <<<

**Dimensional Units** All dimensions are expressed in inches except those shown in brackets (xxx) are expressed in millimeters

"REF." or an Asterisk (\*) = Non-Toleranced Reference Dimension, shown for clarification purposes only.

Used On or Ref.: Scale: **1:1** Drawn By: **G.A** Date Drawn: **3/24/04** Responsible Engineer:

**PROPRIETARY INFORMATION** This Engineering Drawing, and the information contained herein, is proprietary to Cole Hersee Company and may not be disclosed, re-produced, or in any other way transferred or communicated to any other party without the express written consent of an authorized representative of Cole Hersee Company.

**DESIGN CONTROL** It is the responsibility of the individual using / referencing this drawing to assure that the noted design revision level agrees with the revision level of the Controlled Document (Master Drawing). This is a NON-CONTROLLED DOCUMENT unless otherwise specifically noted.

DO NOT SCALE - Dimensional variation may occur during printing / reproduction.

**Key for Special Characteristics:**

Ⓢ Critical Characteristic, relating to Safety and/or Regulatory Compliance

Ⓧ Significant Characteristic relating to Process Control (SPC)

Ⓢ Control Dimension relating to Form - Fit - Function as defined by Cole Hersee Company and/or the Customer

(Note that the identification of any Characteristics as being "Special" does not alter the requirement that ALL specified dimensions & tolerances must be met.)

**Cole Hersee Co.**  
 20 Old Colony Ave., South Boston, MA, 02127  
 Phn: 617-268-2100 Web: www.colehersee.com

Description: **ROCKER SWITCH**

Drawing / Part No.: **58312 CHART** Current Rev. SEE PG 1

Pg. 3 of 4