



- NOTES:
 1). RATING: NO: 14Vdc/20A
 2). TEMPERATURE RANGE: -40C TO 125C
 3). RELAY IS FLUX-TIGHT.
 4). ALL DIMENSIONS SHOWN FOR REFERENCE ONLY.

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE			
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

COPIES TO		MATERIAL SPEC	
1	9	18	FINISH
2	10	19	
3	12	20	
4	13	21	DRW CAD
5	14	23	CHK
6	15	33	DATE
7	16	43	DATE
8	17	53	DATE

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-PM)		GRAMS/PIECE	
DIMENSION	0.5 - 1.5	0.5 - 1.5	0.5 - 1.5
TOLERANCE	±0.10	±0.05	±0.15
3RD ANGLE PROJECTION			
TITLE	SINGLE POLE, NORMALLY OPEN		
TITLE	MINI-MICRO RELAY		
REVISION	DRWG. NO.		

Littelfuse
 DES PLAINES, ILLINOIS 60016

REVISION B 02040080Z