

Schottky Diode

$$V_{RRM} = 200\text{ V}$$


$$I_{FAV} = 2 \times 100\text{ A}$$

$$V_F = 0.84\text{ V}$$

High Performance Schottky Diode
 Low Loss and Soft Recovery
 Parallel legs


Part number

DSS2x101-02A



Backside: isolated

 E72873



Features / Advantages:

- Very low V_f
- Extremely low switching losses
- Low I_{rm} values
- Improved thermal behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching

Applications:

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

Package: SOT-227B (minibloc)

- Isolation Voltage: 3000 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Base plate: Copper internally DCB isolated
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.




| Schottky | | | | Ratings | | | |
|------------|--|--|--------------------|------------------------------|------|------|------|
| Symbol | Definition | Conditions | | min. | typ. | max. | Unit |
| V_{RSM} | max. non-repetitive reverse blocking voltage | | | | | 200 | V |
| V_{RRM} | max. repetitive reverse blocking voltage | | | | | 200 | V |
| I_R | reverse current, drain current | $V_R = 200\text{ V}$ | | $T_{VJ} = 25^\circ\text{C}$ | | 4 | mA |
| | | $V_R = 200\text{ V}$ | | $T_{VJ} = 125^\circ\text{C}$ | | 10 | mA |
| V_F | forward voltage drop | $I_F = 100\text{ A}$ | | $T_{VJ} = 25^\circ\text{C}$ | | 0.94 | V |
| | | $I_F = 200\text{ A}$ | | | | 1.16 | V |
| | | $I_F = 100\text{ A}$ | | $T_{VJ} = 125^\circ\text{C}$ | | 0.84 | V |
| | | $I_F = 200\text{ A}$ | | | | 1.11 | V |
| I_{FAV} | average forward current | $T_C = 105^\circ\text{C}$ | rectangular | $T_{VJ} = 150^\circ\text{C}$ | | 100 | A |
| V_{FO} | threshold voltage | } for power loss calculation only | | | | 0.54 | V |
| r_F | slope resistance | | | | | 2.7 | mΩ |
| R_{thJC} | thermal resistance junction to case | | | | | 0.4 | K/W |
| R_{thCH} | thermal resistance case to heatsink | | | | | 0.1 | K/W |
| P_{tot} | total power dissipation | | | $T_C = 25^\circ\text{C}$ | | 310 | W |
| I_{FSM} | max. forward surge current | $t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}; V_R = 0\text{ V}$ | | $T_{VJ} = 45^\circ\text{C}$ | | 1.40 | kA |
| C_J | junction capacitance | $V_R = 24\text{ V}$ | $f = 1\text{ MHz}$ | $T_{VJ} = 25^\circ\text{C}$ | | 787 | pF |



| Package SOT-227B (minibloc) | | | | Ratings | | | |
|-----------------------------|--|----------------------|-------------------------------------|---------|------|------|--|
| Symbol | Definition | Conditions | min. | typ. | max. | Unit | |
| I_{RMS} | RMS current | per terminal | | | 150 | A | |
| T_{VJ} | virtual junction temperature | | -40 | | 150 | °C | |
| T_{op} | operation temperature | | -40 | | 125 | °C | |
| T_{stg} | storage temperature | | -40 | | 150 | °C | |
| Weight | | | | | 30 | g | |
| M_D | mounting torque | | 1.1 | | 1.5 | Nm | |
| M_T | terminal torque | | 1.1 | | 1.5 | Nm | |
| $d_{Spp/App}$ | creepage distance on surface striking distance through air | terminal to terminal | 10.5 | 3.2 | | mm | |
| $d_{Spb/Apb}$ | | terminal to backside | 8.6 | 6.8 | | mm | |
| V_{ISOL} | isolation voltage | t = 1 second | | 3000 | | V | |
| | | t = 1 minute | 50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA | 2500 | | V | |

Product Marking



| Ordering | Ordering Number | Marking on Product | Delivery Mode | Quantity | Code No. |
|----------|-----------------|--------------------|---------------|----------|----------|
| Standard | DSS2x101-02A | DSS2x101-02A | Tube | 10 | 500867 |

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 150^{\circ}C$




Schottky


| | | | |
|--------------|--------------------|------|----|
| $V_{0\ max}$ | threshold voltage | 0.54 | V |
| $R_{0\ max}$ | slope resistance * | 0.8 | mΩ |



Outlines SOT-227B (minibloc)



| Dim. | Millimeter | | Inches | |
|------|------------|-------|--------|-------|
| | min | max | min | max |
| A | 31.50 | 31.88 | 1.240 | 1.255 |
| B | 7.80 | 8.20 | 0.307 | 0.323 |
| C | 4.09 | 4.29 | 0.161 | 0.169 |
| D | 4.09 | 4.29 | 0.161 | 0.169 |
| E | 4.09 | 4.29 | 0.161 | 0.169 |
| F | 14.91 | 15.11 | 0.587 | 0.595 |
| G | 30.12 | 30.30 | 1.186 | 1.193 |
| H | 37.80 | 38.23 | 1.488 | 1.505 |
| J | 11.68 | 12.22 | 0.460 | 0.481 |
| K | 8.92 | 9.60 | 0.351 | 0.378 |
| L | 0.74 | 0.84 | 0.029 | 0.033 |
| M | 12.50 | 13.10 | 0.492 | 0.516 |
| N | 25.15 | 25.42 | 0.990 | 1.001 |
| O | 1.95 | 2.13 | 0.077 | 0.084 |
| P | 4.95 | 6.20 | 0.195 | 0.244 |
| Q | 26.54 | 26.90 | 1.045 | 1.059 |
| R | 3.94 | 4.42 | 0.155 | 0.167 |
| S | 4.55 | 4.85 | 0.179 | 0.191 |
| T | 24.59 | 25.25 | 0.968 | 0.994 |
| U | -0.05 | 0.10 | -0.002 | 0.004 |
| V | 3.20 | 5.50 | 0.126 | 0.217 |
| W | 19.81 | 21.08 | 0.780 | 0.830 |
| Z | 2.50 | 2.70 | 0.098 | 0.106 |





Schottky




Fig. 1 Max. forward voltage drop characteristics




Fig. 2 Typ. reverse current I_R vs. reverse voltage V_R




Fig. 3 Typ. junction capacitance C_T vs. reverse voltage V_R




Fig. 4 Average forward current $I_{F(AV)}$ vs. case temperature T_C




Fig. 5 Forward power loss characteristics




Fig. 6 Transient thermal impedance junction to case at various duty cycles

Note: All curves are per diode