

# SiC Power MOSFET


$$I_{D25} = 68 \text{ A}$$

$$V_{DSS} = 1200 \text{ V}$$


$$R_{DS(on) \text{ max}} = 34 \text{ m}\Omega$$

Kelvin Source gate connection

**Part number**  
IXFN70N120SK



Backside: isolated  
 E72873



### Features / Advantages:

- High speed switching with low capacitances
- High blocking voltage with low  $R_{DS(on)}$
- Easy to parallel and simple to drive
- Resistant to latch-up
- Real Kelvin source connection

### Applications:

- Solar inverters
- High voltage DC/DC converters
- Motor drives
- Switch mode power supplies
- UPS
- Battery chargers
- Induction heating

### Package: SOT-227B (minibloc)

- Isolation Voltage: 2500 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Base plate with Aluminium nitride isolation
- Advanced power cycling

### Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).

MOSFET				Ratings		
Symbol	Definitions	Conditions	min.	typ.	max.	
$V_{DSS}$	drain source breakdown voltage	$V_{GS} = 0\text{ V}$ , $I_D = 100\ \mu\text{A}$	1200			V
$V_{GSM}$	max transient gate source voltage		-10		+25	V
$V_{GS}$	continous gate source voltage	recommended operational value	-5		+20	V
$I_{D25}$	drain current	$V_{GS} = 20\text{ V}$			68	A
$I_{D80}$					55	A
$I_{D100}$					48	A
$I_{D(pulse)}$	pulsed drain current	pulse width limited by $T_{VJ\max}$			170	A
$P_D$	power dissipation	$T_C = 25^\circ\text{C}$ , $T_{VJ} = 175^\circ\text{C}$			333	W
$R_{DSon}$	static drain source on resistance	$I_D = 50\text{ A}$ ; $V_{GS} = 20\text{ V}$		25 52	34	mΩ mΩ
$V_{GS(th)}$	gate threshold voltage	$I_D = 15\text{ mA}$ ; $V_{GS} = V_{DS}$	2.0	2.6 2.1	4.0	V V
$I_{DSS}$	drain source leakage current	$V_{DS} = 1200\text{ V}$ ; $V_{GS} = 0\text{ V}$		2	100	μA
$I_{GSS}$	gate source leakage current	$V_{DS} = 0\text{ V}$ ; $V_{GS} = 20\text{ V}$			0.6	μA
$R_G$	internal gate resistance	$f = 1\text{ MHz}$ , $V_{AC} = 25\text{ mV}$ , ESR of $C_{ISS}$		1.1		Ω
$C_{ISS}$	input capacitance			2790		pF
$C_{OSS}$	output capacitance	$V_{DS} = 1000\text{ V}$ ; $V_{GS} = 0\text{ V}$ ; $f = 1\text{ MHz}$		220		pF
$C_{RSS}$	reverse transfer (Miller) capacitance	$T_{VJ} = 25^\circ\text{C}$		15		pF
$Q_g$	total gate charge			161		nC
$Q_{gs}$	gate source charge	$V_{DS} = 800\text{ V}$ ; $I_D = 50\text{ A}$ ; $V_{GS} = -5/20\text{ V}$		46		nC
$Q_{gd}$	gate drain (Miller) charge	$T_{VJ} = 25^\circ\text{C}$		50		nC
$t_{d(on)}$	turn-on delay time			30		ns
$t_r$	current rise time			15		ns
$t_{d(off)}$	turn-off delay time	Inductive switching		82		ns
$t_f$	current fall time	$V_{DS} = 800\text{ V}$ ; $I_D = 50\text{ A}$		27		ns
$E_{on}$	turn-on energy per pulse	$V_{GS} = -5 / 20\text{ V}$ ; $R_G = 15\ \Omega$ (external)		1.35		mJ
$E_{off}$	turn-off energy per pulse	Freewheeling diode is Mosfet's body diode		0.76		mJ
$E_{rec(off)}$	reverse recovery losses at turn-off			0.13		mJ
$t_{d(on)}$	turn-on delay time			28		ns
$t_r$	current rise time			12		ns
$t_{d(off)}$	turn-off delay time	Inductive switching		125		ns
$t_f$	current fall time	$V_{DS} = 800\text{ V}$ ; $I_D = 50\text{ A}$		28		ns
$E_{on}$	turn-on energy per pulse	$V_{GS} = -5 / 20\text{ V}$ ; $R_G = 15\ \Omega$ (external)		1.71		mJ
$E_{off}$	turn-off energy per pulse	Freewheeling diode is Mosfet's body diode		0.78		mJ
$E_{rec(off)}$	reverse recovery losses at turn-off			0.29		mJ
$R_{thJC}$	thermal resistance junction to case				0.45	K/W
$R_{thJH}$	thermal resistance junction to heatsink	with heatsink compound; IXYS test setup		0.6		K/W

Source-Drain Diode				Ratings		
Symbol	Definitions	Conditions	min.	typ.	max.	
$V_{SD}$	forward voltage drop	$I_F = 50\text{ A}$ ; $V_{GS} = -5\text{ V}$		4.3 3.7		V V
$t_{rr}$	reverse recovery time			35		ns
$Q_{RM}$	reverse recovery charge (intrinsic diode)	$V_{GS} = -5\text{ V}$ ; $I_F = 50\text{ A}$ ; $V_R = 800\text{ V}$		0.52		μC
$I_{RM}$	max. reverse recovery current	Mosfet gate drive: $V_{GS} = -5 / 20\text{ V}$ ; $R_G = 15\ \Omega$		33		A
$di_F/dt$	current slew rate			3380		A/μs
$t_{rr}$	reverse recovery time			30		ns
$Q_{RM}$	reverse recovery charge (intrinsic diode)	$V_{GS} = -5\text{ V}$ ; $I_F = 50\text{ A}$ ; $V_R = 800\text{ V}$		1.23		μC
$I_{RM}$	max. reverse recovery current	Mosfet gate drive: $V_{GS} = -5 / 20\text{ V}$ ; $R_G = 15\ \Omega$		59		A
$di_F/dt$	current slew rate			4250		A/μs

**Note:** When using SiC Body Diode the maximum recommended  $V_{GS} = -5\text{V}$


IXYS reserves the right to change limits, test conditions and dimensions.

20221012e


Package Outlines SOT-227B (minibloc)			Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.	Unit
$I_{RMS}$	RMS current	per terminal			100	A
$T_{stg}$	storage temperature		-40		150	°C
$T_{op}$	operation temperature		-40		150	°C
$T_{vJ}$	virtual junction temperature		-40		175	°C
<b>Weight</b>				30		g
$M_D$	mounting torque <sup>1)</sup>	screws to heatsink terminal connection screws			1.5 1.3	Nm Nm
$d_{Spp}$	creepage distance on surface	terminal to terminal	10.5			mm
$d_{Spb}$		terminal to backside	8.5			mm
$d_{App}$	striking distance through air	terminal to terminal	3.2			mm
$d_{Apb}$		terminal to backside	6.8			mm
$V_{ISOL}$	isolation voltage	$I_{ISOL} \leq 1 \text{ mA}; 50/60 \text{ Hz}$	3000 2500			V V
$C_p$	coupling capacity per switch	between drain and back side metallization with gate and source shorted		42		pF

<sup>1)</sup> further information see application note IXAN0073 on [www.ixys.com/TechnicalSupport/appnotes.aspx](http://www.ixys.com/TechnicalSupport/appnotes.aspx) (General / Isolation, Mounting, Soldering, Cooling)


## Product Marking



Ordering	Part Name	Marking on Product	Delivering Mode	Base Qty	Ordering Code
Standard	IXFN70N120SK	IXFN70N120SK	Tube	10	IXFN70N120SK

**Outlines SOT-227B (minibloc)**


Dim.	Millimeter		Inches	
	min	max	min	max
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	37.80	38.23	1.488	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.74	0.84	0.029	0.033
M	12.50	13.10	0.492	0.516
N	25.15	25.42	0.990	1.001
O	1.95	2.13	0.077	0.084
P	4.95	6.20	0.195	0.244
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.167
S	4.55	4.85	0.179	0.191
T	24.59	25.25	0.968	0.994
U	-0.05	0.10	-0.002	0.004
V	3.20	5.50	0.126	0.217
W	19.81	21.08	0.780	0.830
Z	2.50	2.70	0.098	0.106



**Curves**




Fig. 1 Typical output characteristics ( $-25^{\circ}\text{C}$ )




Fig. 2 Typical output characteristics ( $25^{\circ}\text{C}$ )




Fig. 3 Typical output characteristics ( $150^{\circ}\text{C}$ )




Fig. 4  $R_{DS(on)}$  normalized vs. junction temperature  $T_{VJ}$




Fig. 5  $R_{DS(on)}$  versus drain current




Fig. 6  $R_{DS(on)}$  versus junction temperature  $T_{VJ}$



**Curves**

 Fig. 7 Norm. breakdow  $V_{DSS}$  & treshhold voltage  $V_{TH}$  versus junction temperature  $T_{VJ}$ 


Fig. 8 Typical transfer characteristics







Fig. 9 Typical forward transconductance


 Fig. 10 Forward voltage drop of intrinsic diode versus  $V_{DS}$  measured at  $-55^{\circ}\text{C}$ 

 Fig. 11 Forward voltage drop of intrinsic diode versus  $V_{DS}$  measured at  $25^{\circ}\text{C}$ 

 Fig. 12 Forward voltage drop of intrinsic diode versus  $V_{DS}$  measured at  $150^{\circ}\text{C}$


**Curves**


Fig. 13 Typical switching energy versus drain current




Fig. 14 Typical switching energy versus temperature




Fig. 15 Typical switching energy versus external gate resistor




Fig. 16 Typical switching time versus external gate resistor




Fig. 17 Typical turn on gate charge, trendline




Fig. 18 Typical transient thermal impedance