

$\varnothing 38.1 \pm 0.18$
 $[\varnothing 1.500 \pm 0.007]$

6.4 ± 0.08
 $[0.250 \pm 0.003]$

10.3 ± 0.13
 $[0.406 \pm 0.005]$

65.1 ± 1.57
 $[2.562 \pm 0.062]$

49.2 ± 1.57
 $[1.938 \pm 0.062]$

31.8
 $[1.250]$

88.9 ± 1.57
 $[3.500 \pm 0.062]$

25.3 ± 0.25
 $[0.995 \pm 0.010]$

REVISION

| REV | DATE | DESCRIPTION |
|-----|---------|-------------------------|
| A | 6/27/23 | 526651GCP - RELEASE MRY |

| 1 | NO | COMPONENT NO | DESCRIPTION | QTY/M | U/M |
|---|----|--------------|-------------|-------|-----|
|---|----|--------------|-------------|-------|-----|

BILL OF MATERIAL

| | | | | | |
|-----|--|--|--|--|----------|
| <S> | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE | | | | |
| ● | DENOTES CRITICAL CHARACTERISTICS. | | | | |
| CPK | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE | | | | |
| ST | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. | | | | |
| CP | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. | | | | A |

| | | | | |
|-----------|--------|--|--|--|
| MATL SPEC | FINISH | | | |
|-----------|--------|--|--|--|

| | | | | |
|---------------|-------------------|--------------|-------------------------------|--|
| DRW JMoler | DATE 6/19/2023 | SCALE NTS | FINISH GOOD WT GRAMS/PIECE | |
|---------------|-------------------|--------------|-------------------------------|--|

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

| | | | | |
|-------------------------|--|--|--|--|
| 3RD ANGLE PROJECTION | | | | |
|-------------------------|--|--|--|--|

TITLE L15S 500-1000A OUTLINE

| | | | |
|-----------------------------|----------|-------------|--------------|
| CHICAGO, ILLINOIS 60631 | REVISION | DRWG NO. | SHEET 1 OF 1 |
| | A | OL-L15S1000 | |