

$\varnothing 33.2 \pm 0.18$   
 $[\varnothing 1.306 \pm 0.007]$

$4.8 \pm 0.08$   
 $[0.188 \pm 0.003]$

$7.9 \pm 0.13$   
 $[0.312 \pm 0.005]$

$95.50 \pm 1.59$   
 $[3.760 \pm 0.063]$

$90.73 \pm 1.59$   
 $[3.572 \pm 0.063]$

$112.2 \pm 1.59$   
 $[4.416 \pm 0.063]$

$74.1 \pm 1.59$   
 $[2.916 \pm 0.063]$

$25.4 \pm 0.20$   
 $[1.000 \pm 0.008]$

REVISION

REV	DATE	DESCRIPTION
A	7/19/23	526717GCP - RELEASE MRY

1	COMPONENT NO	DESCRIPTION	QTY/M	U/M
---	--------------	-------------	-------	-----

**BILL OF MATERIAL**

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			<b>A</b>

MATL SPEC		FINISH		
DRW JMoler	DATE 6/23/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION



**TITLE** L60S 125-200A OUTLINE



REVISION <b>A</b>	DRWG NO. <b>OL-L60S200</b>	SHEET 1 OF 1
----------------------	-------------------------------	--------------