


| TERMINAL | NO. WIRES PER TERMINAL | WIRE RANGE | SOLID WIRE | STRANDED WIRE |
|----------|------------------------|------------|------------|---------------|
| A        | 1                      | #12-8      | X          | X             |
|          | 2                      | #12        | X          | X             |

| REVISION |         |                         |
|----------|---------|-------------------------|
| REV      | DATE    | DESCRIPTION             |
| A        | 1/16/23 | 526124GCP - RELEASE MRY |



RECOMMENDED CRIMP TOOL:  
 A TERMINAL- T&B WT161M,  
 1 CRIMP

STRIP WIRES 1".  
 CRIMP 1/4" FROM END

NOTES:

- PRODUCT IS UL RECOGNIZED
- MATERIAL TYPE: BODY: BLACK, FLAME RETARDANT, GLASS FIBER REINFORCED, POLYESTER RESIN  
 TERMINALS: TIN-PLATED COPPER  
 FUSE CLIPS: TIN-PLATED BRASS  
 SPRING: STAINLESS STEEL  
 SCREW: ZINC-PLATED STEEL

| NO  | COMPONENT NO  | DESCRIPTION  | QTY/M                      | U/M          |
|---|---|--|----------------------------|--------------|
| <b>BILL OF MATERIAL</b>   |   |  |                            |              |
| <S>   |   | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE   |                            |              |
| ●   |   | DENOTES CRITICAL CHARACTERISTICS.  |                            |              |
| CPK   |   | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE   |                            |              |
| Ⓢ   |   | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |                            |              |
| CP  |   | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |                            | <b>B</b>     |
| MATL SPEC   |   | FINISH   |                            |              |
| DRW myork   | DATE 1/13/23  | SCALE NTS  | FINISH GOOD WT GRAMS/PIECE |              |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 |   |  |                            |              |
| 3RD ANGLE PROJECTION  | TOLERANCE UNLESS OTHERWISE SPECIFIED<br>ONE PLACE DEC ± .25 [.01] FRACTION ±<br>TWO PLACE DEC ± .100 [.004] ANGULAR ±1° |  |                            |              |
| TITLE   |   | OLEX00AAX OUTLINE  |                            |              |
| CHICAGO, ILLINOIS 60631   |   | REVISION<br>A  | DRWG NO.<br>OL-OLEXAA      | SHEET 1 OF 1 |