



Insulated Gate Bi-Polar Transistor Type T2000BB45G

Absolute Maximum Ratings

	VOLTAGE RATINGS	MAXIMUM LIMITS	UNITS
V _{CES}	Collector – emitter voltage	4500	V
V _{DC link}	Permanent DC voltage for 100 FIT failure rate.	2800	V
V _{GES}	Peak gate – emitter voltage	±20	V

	RATINGS	MAXIMUM LIMITS	UNITS
I _C	DC collector current, IGBT	2000	A
I _{CRM}	Repetitive peak collector current, t _p =1ms, IGBT	4000	A
I _{F(DC)}	Continuous DC forward current, Diode	2000	A
I _{FRM}	Repetitive peak forward current, t _p =1ms, Diode	4000	A
I _{FSM}	Peak non-repetitive surge t _p =10ms, V _{RM} =60%V _{RRM} , Diode (Note 4)	52.3	kA
I _{FSM2}	Peak non-repetitive surge t _p =10ms, V _{RM} ≤10V, Diode (Note 4)	57.5	kA
P _{MAX}	Maximum power dissipation, IGBT (Note 2)	15.5	kW
(di/dt) _{cr}	Critical diode di/dt (note 3)	4000	A/μs
T _j	Operating temperature range.	-40 to +125	°C
T _{stg}	Storage temperature range.	-40 to +125	°C

Notes: -

- 1) Unless otherwise indicated T_j = 125°C.
- 2) T_{sink} = 25°C, double side cooled.
- 3) Maximum commutation loop inductance 180nH.
- 4) Half-sinewave, 125°C T_j initial.

Characteristics

IGBT Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
V _{CE(sat)}	Collector – emitter saturation voltage	-	2.7	3.1	I _C = 2000A, V _{GE} = 15V, T _j = 25°C	V
		-	3.5	3.9	I _C = 2000A, V _{GE} = 15V	V
V _{T0}	Threshold voltage	-	-	1.76	Current range: 667A – 2000A	V
r _T	Slope resistance	-	-	1.07		mΩ
V _{GE(TH)}	Gate threshold voltage	-	5.1	-	V _{CE} = V _{GE} , I _C = 205mA	V
I _{CES}	Collector – emitter cut-off current	-	65	90	V _{CE} = V _{CES} , V _{GE} = 0V	mA
I _{GES}	Gate leakage current	-	-	±23	V _{GE} = ±20V	μA
C _{ies}	Input capacitance	-	317	-	V _{CE} = 25V, V _{GE} = 0V, f = 1MHz	nF
t _{d(on)}	Turn-on delay time	-	1.7	-	I _C = 2000A, V _{CE} = 2800V, di/dt = 3500A/μs V _{GE} = ±15V, L _S = 180nH R _{g(ON)} = 2.7Ω, R _{g(OFF)} = 12Ω, C _{GE} = 220nF Integral diode used as freewheel diode (Note 3 & 4)	μs
t _{r(V)}	Rise time	-	3.8	-		μs
Q _{g(on)}	Turn-on gate charge	-	14.5	-		μC
E _{on}	Turn-on energy	-	14	-		J
t _{d(off)}	Turn-off delay time	-	5.5	-		μs
t _{f(I)}	Fall time	-	2.8	-		μs
Q _{g(off)}	Turn-off gate charge	-	11	-		μC
E _{off}	Turn-off energy	-	12.5	-		J
I _{SC}	Short circuit current	-	7800	-		V _{GE} = +15V, V _{CC} = 2800V, V _{CEmax} ≤ V _{CES} , t _p ≤ 10μs

Diode Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
V _F	Forward voltage	-	3.35	3.65	I _F = 2000A, T _j = 25°C	V
		-	3.55	3.85	I _F = 2000A	V
V _{To}	Threshold voltage	-	-	2.08	Current range 667A - 2000A	V
r _T	Slope resistance	-	-	0.88		mΩ
I _{rm}	Peak reverse recovery current	-	2050	-	I _F = 2000A, V _r = 2800V, V _{GE} = -15V, di/dt = 3500A/μs	A
Q _{rr}	Recovered charge	-	2450	-		μC
t _{rr}	Reverse recovery time, 50% chord	-	1.6	-		μs
E _r	Reverse recovery energy	-	3.6	-		J

Thermal Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
R _{thJK}	Thermal resistance junction to sink, IGBT	-	-	6.45	Double side cooled	K/kW
		-	-	10.5	Collector side cooled	K/kW
		-	-	16.8	Emitter side cooled	K/kW
R _{thJK}	Thermal resistance junction to sink, Diode	-	-	9.65	Double side cooled	K/kW
		-	-	14.9	Cathode side cooled	K/kW
		-	-	27.4	Anode side cooled	K/kW
F	Mounting force	60	-	85	Note 2	kN
W _t	Weight	-	2.4	-		kg

Notes:-

- 1) Unless otherwise indicated T_j = 125°C.
- 2) Consult application note 2008AN01 for detailed mounting requirements
- 3) C_{GE} is additional gate – emitter capacitance added to output of gate drive
- 4) Figures 6 to 9 are obtained using integral diode as freewheeling diode

Curves

Figure 1 – Typical collector-emitter saturation voltage characteristics




Figure 2 – Typical output characteristic




Figure 3 – Typical output characteristic




Figure 4 – Typical turn-on delay time vs gate resistance




Figure 5 – Typical turn-off delay time vs. gate resistance




Figure 6 – Typical turn-on energy vs. collector current




Figure 7 – Typical turn-on energy vs. di/dt




Figure 8 – Typical turn-off energy vs. collector current




Figure 9 – Turn-off energy vs voltage




Figure 10 – Safe operating area (IGBT)




Figure 11 – Typical diode forward characteristics




Figure 12 – Typical recovered charge




Figure 13 – Typical reverse recovery current




Figure 14 – Typical reverse recovery time




Figure 15 – Typical reverse recovery energy




Figure 16 – Safe operating area (Diode)




Figure 17 – Transient thermal impedance (IGBT)





Figure 18 – Transient thermal impedance (Diode)



Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics