


GenX3™ 600V IGBT w/ Diode

IXGH56N60B3D1


$V_{CES} = 600V$
 $I_{C110} = 56A$
 $V_{CE(sat)} \leq 1.80V$

Medium-Speed-Low-Vsat PT
IGBT 5-40kHz Switching



| Symbol | Test Conditions | Maximum Ratings | |
|-------------------------------|---|---|------------|
| V_{CES} | $T_J = 25^\circ C$ to $150^\circ C$ | 600 | V |
| V_{CGR} | $T_J = 25^\circ C$ to $150^\circ C$, $R_{GE} = 1M\Omega$ | 600 | V |
| V_{GES} | Continuous | ± 20 | V |
| V_{GEM} | Transient | ± 30 | V |
| I_{C110} | $T_C = 110^\circ C$ | 56 | A |
| I_{CM} | $T_C = 25^\circ C$, 1ms | 350 | A |
| SSOA (RBSOA) | $V_{GE} = 15V$, $T_{VJ} = 125^\circ C$, $R_G = 5\Omega$ Clamped Inductive Load | $I_{CM} = 150$ @ $V_{CE} \leq V_{CES}$ | A |
| P_C | $T_C = 25^\circ C$ | 330 | W |
| T_J | | -55 ... +150 | $^\circ C$ |
| T_{JM} | | 150 | $^\circ C$ |
| T_{stg} | | -55 ... +150 | $^\circ C$ |
| T_L | Maximum Lead Temperature for Soldering | 300 | $^\circ C$ |
| T_{SOLD} | 1.6 mm (0.062in.) from Case for 10s | 260 | $^\circ C$ |
| M_d | Mounting Torque | 1.13/10 | Nm/lb.in. |
| Weight | | 6 | g |

TO-247



G = Gate C = Collector
 E = Emitter Tab = Collector

Features

- Optimized for Low Conduction and Switching losses
- Square RBSOA
- Anti-Parallel Ultra Fast Diode
- International Standard Package

Advantages

- High Power Density
- Low Gate Drive Requirement

Applications

- Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts

| Symbol | Test Conditions ($T_J = 25^\circ C$, Unless Otherwise Specified) | Characteristic Values | | |
|---------------|---|-----------------------|--------------|---------------------|
| | | Min. | Typ. | Max. |
| $V_{GE(th)}$ | $I_C = 250\mu A$, $V_{CE} = V_{GE}$ | 3.0 | | 5.0 V |
| I_{CES} | $V_{CE} = V_{CES}$, $V_{GE} = 0V$ $T_J = 125^\circ C$ | | | 300 μA 2 mA |
| I_{GES} | $V_{CE} = 0V$, $V_{GE} = \pm 20V$ | | | ± 100 nA |
| $V_{CE(sat)}$ | $I_C = 44A$, $V_{GE} = 15V$, Note 1 $T_J = 125^\circ C$ | | 1.49 1.47 | 1.80 V V |


Symbol Test Conditions

($T_J = 25^\circ\text{C}$ Unless Otherwise Specified)

Characteristic Values

| | | Min. | Typ. | Max. | |
|--------------|---|------|------|-------|--------------------|
| g_{fs} | $I_C = 44\text{A}, V_{CE} = 10\text{V}, \text{Note 1}$ | 36 | 60 | | S |
| C_{ies} | $V_{CE} = 25\text{V}, V_{GE} = 0\text{V}, f = 1\text{MHz}$ | | 3950 | | pF |
| C_{oes} | | | 220 | | pF |
| C_{res} | | | 56 | | pF |
| $Q_{g(on)}$ | $I_C = 40\text{A}, V_{GE} = 15\text{V}, V_{CE} = 0.5 \cdot V_{CES}$ | | 138 | | nC |
| Q_{ge} | | | 25 | | nC |
| Q_{gc} | | | 47 | | nC |
| $t_{d(on)}$ | Inductive Load, $T_J = 25^\circ\text{C}$ $I_C = 44\text{A}, V_{GE} = 15\text{V}$ $V_{CE} = 480\text{V}, R_G = 5\Omega$ Note 2 | | 26 | | ns |
| t_{ri} | | | 41 | | ns |
| E_{on} | | | 1.30 | | mJ |
| $t_{d(off)}$ | | | 155 | 335 | ns |
| t_{fi} | | | 95 | 165 | ns |
| E_{off} | | | 1.05 | 2.0 | mJ |
| $t_{d(on)}$ | Inductive Load, $T_J = 125^\circ\text{C}$ $I_C = 44\text{A}, V_{GE} = 15\text{V}$ $V_{CE} = 480\text{V}, R_G = 5\Omega$ Note 2 | | 26 | | ns |
| t_{ri} | | | 37 | | ns |
| E_{on} | | | 2.34 | | mJ |
| $t_{d(off)}$ | | | 220 | | ns |
| t_{fi} | | | 165 | | ns |
| E_{off} | | | 2.20 | | mJ |
| R_{thJC} | | | | 0.375 | $^\circ\text{C/W}$ |
| R_{thCS} | | 0.21 | | | $^\circ\text{C/W}$ |

TO-247 (IXGH) Outline



| Dim. | Millimeter | | Inches | |
|------|------------|-------|-----------|-------|
| | min | max | min | max |
| A | 4.70 | 5.30 | 0.185 | 0.209 |
| A1 | 2.21 | 2.59 | 0.087 | 0.102 |
| A2 | 1.50 | 2.49 | 0.059 | 0.098 |
| b | 0.99 | 1.40 | 0.039 | 0.055 |
| b2 | 1.65 | 2.39 | 0.065 | 0.094 |
| b4 | 2.59 | 3.43 | 0.102 | 0.135 |
| c | 0.38 | 0.89 | 0.015 | 0.035 |
| D | 20.79 | 21.45 | 0.819 | 0.845 |
| D1 | 13.07 | - | 0.515 | - |
| D2 | 0.51 | 1.35 | 0.020 | 0.053 |
| E | 15.48 | 16.24 | 0.610 | 0.640 |
| E1 | 13.45 | - | 0.53 | - |
| E2 | 4.31 | 5.48 | 0.170 | 0.216 |
| e | 5.45 BSC | | 0.215 BSC | |
| L | 19.80 | 20.30 | 0.078 | 0.800 |
| L1 | - | 4.49 | - | 0.177 |
| Ø P | 3.55 | 3.65 | 0.140 | 0.144 |
| Ø P1 | - | 7.39 | - | 0.290 |
| Q | 5.38 | 6.19 | 0.212 | 0.244 |
| S | 6.14 BSC | | 0.242 BSC | |

Reverse Diode (FRED)

Symbol Test Conditions

($T_J = 25^\circ\text{C}$ Unless Otherwise Specified)

Characteristic Values

| | | Min. | Typ. | Max. | |
|------------|---|------|------|------|--------------------|
| V_F | $I_F = 30\text{A}, V_{GE} = 0\text{V}, \text{Note 1}$ | | | 2.7 | V |
| | | | | | V |
| I_{RM} | $I_F = 30\text{A}, V_{GE} = 0\text{V}, -di_F/dt = 100\text{A}/\mu\text{s}, T_J = 100^\circ\text{C}$ | | 1.6 | 4 | A |
| t_{rr} | $V_R = 100\text{V}, T_J = 100^\circ\text{C}$ | | 100 | | ns |
| | $I_F = 1\text{A}, V_{GE} = 0\text{V}, -di_F/dt = 100\text{A}/\mu\text{s}, V_R = 30\text{V}$ | | 25 | | ns |
| R_{thJC} | | | | 0.9 | $^\circ\text{C/W}$ |

Notes:

1. Pulse test, $t \leq 300\mu\text{s}$, duty cycle, $d \leq 2\%$.
2. Switching times & energy losses may increase for higher V_{CE} (clamp), T_J or R_G .

IXYS Reserves the Right to Change Limits, Test Conditions and Dimensions.

| | | | | | | | | | | |
|--|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665 | 6,404,065 B1 | 6,683,344 | 6,727,585 | 7,005,734 B2 | 7,157,338B2 |
| | 4,860,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343 | 6,710,405 B2 | 6,759,692 | 7,063,975 B2 | |
| | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505 | 6,710,463 | 6,771,478 B2 | 7,071,537 | |







Fig. 1. Output Characteristics @ 25°C

Fig. 2. Extended Output Characteristics @ 25°C

Fig. 3. Output Characteristics @ 125°C

Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature

Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage

Fig. 6. Input Admittance


Fig. 7. Transconductance




Fig. 8. Gate Charge




Fig. 9. Capacitance




Fig. 10. Reverse-Bias Safe Operating Area




Fig. 11. Maximum Transient Thermal Impedance













Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance

Fig. 13. Inductive Switching Energy Loss vs. Collector Current

Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature

Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance

Fig. 16. Inductive Turn-off Switching Times vs. Collector Current

Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature


Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance

Fig. 19. Inductive Turn-on Switching Times vs. Collector Current

Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature





Fig. 21. Forward Current I_F Versus V_F




Fig. 22. Reverse Recovery Charge Q_r Versus $-di_F/dt$




Fig. 23. Peak Reverse Current I_{RM} Versus $-di_F/dt$




Fig. 24. Dynamic Parameters Q_r , I_{RM} Versus T_{VJ}




Fig. 25. Recovery Time t_{rr} Versus $-di_F/dt$




Fig. 26. Peak Forward Voltage V_{FR} and t_{rr} Versus di_F/dt




Fig. 27. Transient Thermal Resistance Junction to Case

Constants for Z_{thJC} calculation:

| i | R_{thi} (K/W) | t_i (s) |
|---|-----------------|-----------|
| 1 | 0.502 | 0.0052 |
| 2 | 0.193 | 0.0003 |
| 3 | 0.205 | 0.0162 |



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.