

# HiPerFET™ Power MOSFETs

N-Channel Enhancement Mode  
Avalanche Rated, High dv/dt, Low  $t_{rr}$


**IXFK 110 N06**  
**IXFK 105 N07**  
**IXFK 110 N07**

$V_{DSS}$	$I_{D25}$	$R_{DS(on)}$
60 V	110 A	6 mΩ
70 V	105 A	7 mΩ
70 V	110 A	6 mΩ

$t_{rr} \leq 250 \text{ ns}$

Symbol	Test Conditions	Maximum Ratings		
$V_{DSS}$	$T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$	N07	70	V
$V_{DGR}$	$T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GS} = 1 \text{ M}\Omega$	N06	60	V
$V_{GS}$	Continuous	N07	70	V
$V_{GSM}$	Transient	N06	60	V
$I_{D25}$	$T_C = 25^\circ\text{C}$ , die capability		110	A
$I_{D130}$	$T_C = 130^\circ\text{C}$ , limited by external leads		76	A
$I_{DM}$	$T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$		600	A
$I_{AR}$	$T_C = 25^\circ\text{C}$		100	A
$E_{AR}$	$T_C = 25^\circ\text{C}$		30	mJ
$E_{AS}$	$T_C = 25^\circ\text{C}$		2	J
dv/dt	$I_S \leq I_{DM}$ , $di/dt \leq 100 \text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ\text{C}$ , $R_G = 2 \Omega$		5	V/ns
$P_D$	$T_C = 25^\circ\text{C}$		500	W
$T_J$			-55 ... +150	$^\circ\text{C}$
$T_{JM}$			150	$^\circ\text{C}$
$T_{stg}$			-55 ... +150	$^\circ\text{C}$
$T_L$	1.6 mm (0.063 in) from case for 10 s		300	$^\circ\text{C}$
$M_d$	Mounting torque		0.9/6	Nm/lb.in.
	Terminal connection torque		-	Nm/lb.in.
Weight			10	g

## TO-264 AA (IXFK)



## Features

- International standard packages
- JEDEC TO-264 AA, epoxy meet UL94 V-0, flammability classification
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
- Fast intrinsic Rectifier

## Applications


- DC-DC converters
- Synchronous rectification
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls
- Low voltage relays

## Advantages

- Easy to mount
- Space savings
- High power density

Symbol	Test Conditions	Characteristic Values ( $T_J = 25^\circ\text{C}$ , unless otherwise specified)		
		min.	typ.	max.
$V_{DSS}$	$V_{GS} = 0 \text{ V}$ , $I_D = 1 \text{ mA}$	N06	60	V
		N07	70	V
$V_{GS(th)}$	$V_{DS} = V_{GS}$ , $I_D = 8 \text{ mA}$		2	4 V
$I_{GSS}$	$V_{GS} = \pm 20 \text{ V}_{DC}$ , $V_{DS} = 0$			$\pm 200 \text{ nA}$
$I_{DSS}$	$V_{DS} = 0.8 \cdot V_{DSS}$ , $V_{GS} = 0 \text{ V}$	$T_J = 25^\circ\text{C}$ $T_J = 125^\circ\text{C}$		400 $\mu\text{A}$ 2 mA
$R_{DS(on)}$	$V_{GS} = 10 \text{ V}$ , $I_D = 0.5 \cdot I_{D25}$ Note 2	110N06/110N07 105N07		6 mΩ 7 mΩ

Symbol	Test Conditions	Characteristic Values ( $T_J = 25^\circ\text{C}$ , unless otherwise specified)		
		min.	typ.	max.
$g_{fs}$	$V_{DS} = 10\text{ V}; I_D = 0.5 \cdot I_{D25}$ , Note 2	60	80	S
$C_{iss}$	$V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$		9000	pF
$C_{oss}$			4000	pF
$C_{rss}$			2400	pF
$t_{d(on)}$	$V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$ $R_G = 1\ \Omega$ (External),		30	ns
$t_r$			60	ns
$t_{d(off)}$			100	ns
$t_f$			60	ns
$Q_{g(on)}$	$V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$		480	nC
$Q_{gs}$			60	nC
$Q_{gd}$			240	nC
$R_{thJC}$	TO-264 AA		0.25	K/W
$R_{thCK}$	TO-264 AA		0.15	K/W

**TO-264 AA Outline**


Dim.	Millimeter		Inches	
	Min.	Max.	Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46	BSC	.215	BSC
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

Symbol	Test Conditions	Characteristic Values ( $T_J = 25^\circ\text{C}$ , unless otherwise specified)		
		min.	typ.	max.
$I_S$	$V_{GS} = 0\text{ V}$	110N06/110N07 105N07		110 A 105 A
$I_{SM}$	Repetitive; pulse width limited by $T_{JM}$	110N06/110N07 105N07		440 A 420 A
$V_{SD}$	$I_F = 100\text{ A}, V_{GS} = 0\text{ V}$ , Note 2			1.7 V
$t_{rr}$	$I_F = 25\text{ A}$ $-di/dt = 100\text{ A}/\mu\text{s}$ $V_R = 50\text{ V}$		150	250 ns
$Q_{RM}$				0.7 $\mu\text{C}$
$I_{RM}$				9 A

Note: 1. Pulse width limited by  $T_{JM}$   
2. Pulse test,  $t \leq 300\ \mu\text{s}$ , duty cycle  $d \leq 2\%$




Figure 1. Output Characteristics at 25°C




Figure 2. Extended Output Characteristics




Figure 3. Admittance Curves




Figure 4. Transconductance vs. Drain Current




Figure 5.  $R_{DS(on)}$  normalized to  $0.5 I_{D25}$  value




Figure 6. Normalized  $R_{DS(on)}$  vs. Junction Temperature




Figure 7. Gate Charge




Figure 8. Drain Current vs. Case Temperature




Figure 9. Capacitance Curves




Figure 10. Source-Drain Voltage vs. Source Current




Figure 11. Transient Thermal Resistance



---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).