

GLASS FHP

32V IN-LINE BAYONET KNOB GLASS FUSE HOLDER



Description

The Glass FHP Series 32V In-Line Bayonet Knob Glass Fuse Holder comes with 3 springs to allow use with glass SFE (7.5, 9, 14, and 20) and AGC (AG3) fuses up to 20 amps. Made with a heat-resistant black thermoset material, the automotive glass fuse holder carries a UL 94 V-0 flammability rating. Its spring-locked, bayonet-type knob helps make installing and replacing a glass tube fuse simple. Plus, the red 15" looped 14 AWG wire makes in-line installation easy.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/GlassFHP

Ordering Information

| PART NUMBER | DESCRIPTION | FUSE TYPE | MOUNTING METHOD | MAX CURRENT RATING | MAX VOLTAGE RATING |
|-------------|--|-----------------|---------------------|--------------------|--------------------|
| 0FHP0001Z | 32V In-Line Bayonet Knob Glass Fuse Holder | Glass SFE Fuses | IN LINE FUSE HOLDER | 20 AMPS | 32 VDC |

Specifications

| | |
|-----------------------------------|------------------------|
| Current Rating Continuous: | 15A |
| Current Rating Max: | 20A |
| Fuse Type: | Glass SFE or 3AG Fuses |
| Flammability Rating: | UL 94 V-0 |
| Mounting Method: | Cable |
| Max Voltage Rating: | 32 VDC |
| Wire Description: | Color Red Stranded |
| Wire Size: | 14 AWG |

Applications

- Accessory Circuits

Features and Benefits

- Includes 3 springs for compatibility with glass SFE (7.5, 9, 14, and 20) and AGC (AG3) fuses up to 20 amps (fuses sold separately)
- Spring-locked, bayonet-type knob for easy fuse replacement
- Red 15" looped 14 AWG wire lead enables simple in-line installation
- Heat-resistant black thermoset material with a UL 94 V-0 flammability rating