


0.020" ± 0.002" DIAMETER,  
24 AWG, TINNED CCS,  
1.0" LONG MINIMUM



RESISTANCE @ 25°C = 1,000,000 ± 5%  
RESISTANCE/TEMPERATURE CURVE = "R"  
BETA (0 TO +50°C) = 4,140°K NOMINAL  
TEMPERATURE COEFFICIENT @ 25°C = -4.68%/°C NOMINAL  
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)  
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)  
THERMAL TIME COSNTANT = 0.5 SECONDS NOMINAL (STIRRED LIQUID)  
MAXIMUM TEMPERATURE RATING = +300°C

---	ISO RELEASE	10/15/04	DD
"A"	LEAD WIRE WAS 0.020" ± 0.001" DIAMETER & 1.125" LONG NOMINAL	10/15/04	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	<b>U.S. SENSOR CORP.</b> 1832 W. COLL INS AVE. ORANGE, CA. 92867 714-639-1000 www.ussensor.com
DRAWN BY R. DANKERT	
DATE 10/14/95	
REV. "A"	
LAYER 0 OF 1	
<b>NTC THERMISTOR</b>	
<b>P/N 105RG1J</b>	