


0.020" ± 0.002" DIAMETER,  
24 AWG, TINNED CCS,  
1.0" LONG MINIMUM



RESISTANCE @ +25°C = 2,500 Ω ± 5%  
RESISTANCE/TEMPERATURE CURVE = "F"  
BETA "β" (0 TO +50°C) = 3,419°K NOMINAL  
TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL  
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)  
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)  
THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED OIL)  
MAXIMUM TEMPERATURE RATING = +300°C

|     |  |          |     |
|-----|--|----------|-----|
| --- | ISO RELEASE  | 12/15/03 | DD  |
| "A" | LEAD WIRE WAS 0.020" ± 0.001" DIAMETER & 1.125" LONG NOMINAL | 12/15/03 | DD  |
| REV | REVISION RECORD  | DATE     | APP |

|                      |  |
|----------------------|--|
| SCALE NONE           | U.S. SENSOR CORP.<br>© COPYRIGHT<br>714-639-1000 www.ussensor.com<br>NTC THERMISTOR<br>P/N 252FG1J |
| DRAWN BY<br>C. PAYAN |  |
| DATE 06/15/99        |  |
| REV "A"              |  |
| LAYER 0 OF 1         |  |