

Schottky Diode

$$V_{RRM} = 15\text{ V}$$


$$I_{FAV} = 2 \times 35\text{ A}$$

$$V_F = 0.35\text{ V}$$


High Performance Schottky Diode
 Low Loss and Soft Recovery
 Common Cathode

Part number

DSSK70-0015B



Backside: cathode



Features / Advantages:

- Very low V_f
- Extremely low switching losses
- Low I_{rm} values
- Improved thermal behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching

Applications:

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

Package: TO-247

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.



Schottky				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V_{RSM}	max. non-repetitive reverse blocking voltage					15	V
V_{RRM}	max. repetitive reverse blocking voltage					15	V
I_R	reverse current, drain current	$V_R = 15\text{ V}$	$T_{VJ} = 25^\circ\text{C}$			20	mA
		$V_R = 15\text{ V}$	$T_{VJ} = 100^\circ\text{C}$			350	mA
V_F	forward voltage drop	$I_F = 35\text{ A}$	$T_{VJ} = 25^\circ\text{C}$			0.46	V
		$I_F = 70\text{ A}$				0.56	V
		$I_F = 35\text{ A}$	$T_{VJ} = 125^\circ\text{C}$			0.35	V
		$I_F = 70\text{ A}$				0.49	V
I_{FAV}	average forward current	$T_C = 130^\circ\text{C}$ rectangular	$T_{VJ} = 150^\circ\text{C}$ d = 0.5			35	A
V_{F0}	threshold voltage	} for power loss calculation only				0.18	V
r_F	slope resistance					4	mΩ
R_{thJC}	thermal resistance junction to case					1.1	K/W
R_{thCH}	thermal resistance case to heatsink				0.25		K/W
P_{tot}	total power dissipation			$T_C = 25^\circ\text{C}$		115	W
I_{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; $V_R = 0\text{ V}$		$T_{VJ} = 45^\circ\text{C}$		500	A
C_J	junction capacitance	$V_R = 3\text{ V}$	f = 1 MHz	$T_{VJ} = 25^\circ\text{C}$		5.01	nF



Package TO-247			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal ¹⁾			70	A
T_{VJ}	virtual junction temperature		-55		150	°C
T_{op}	operation temperature		-55		125	°C
T_{stg}	storage temperature		-55		150	°C
Weight				6		g
M_D	mounting torque		0.8		1.2	Nm
F_C	mounting force with clip		20		120	N

Product Marking



Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DSSK70-0015B	DSSK70-0015B	Tube	30	476196

Equivalent Circuits for Simulation

** on die level*

$T_{VJ} = 150^{\circ}C$



Schottky


$V_{0\ max}$	threshold voltage	0.18	V
$R_{0\ max}$	slope resistance *	1.5	mΩ



Outlines TO-247



Sym.	Inches		Millimeter	
	min.	max.	min.	max.
A	0.185	0.209	4.70	5.30
A1	0.087	0.102	2.21	2.59
A2	0.059	0.098	1.50	2.49
D	0.819	0.845	20.79	21.45
E	0.610	0.640	15.48	16.24
E2	0.170	0.216	4.31	5.48
e	0.215	BSC	5.46	BSC
L	0.780	0.800	19.80	20.30
L1	-	0.177	-	4.49
Ø P	0.140	0.144	3.55	3.65
Q	0.212	0.244	5.38	6.19
S	-	0.242	-	6.14
b	0.039	0.055	0.99	1.40
b2	0.065	0.094	1.65	2.39
b4	0.102	0.135	2.59	3.43
c	0.015	0.035	0.38	0.89
D1	0.515	-	13.07	-
D2	0.020	0.053	0.51	1.35
E1	0.530	-	13.45	-
Ø P1	-	0.29	-	7.39



Schottky




Fig. 1 Max. forward voltage drop characteristics




Fig. 2 Typ. reverse current I_R vs. reverse voltage V_R




Fig. 3 Typ. junction capacitance C_T vs. reverse voltage V_R




Fig. 4 Average forward current $I_{F(AV)}$ vs. case temp. T_C




Fig. 5 Forward power loss characteristics




Fig. 6 Transient thermal impedance junction to case at various duty cycles

Note: All curves are per diode