

# Thyristor Modules


## ECO-PAC 2

$$I_{TRMS} = 280 \text{ A}$$

$$I_{TAVM} = 180 \text{ A}$$

$$V_{RRM} = 1200/1600 \text{ V}$$

$V_{RSM}$	$V_{RRM}$	Typ
$V_{DSM}$ V	$V_{DRM}$ V	
1300	1200	VCO 180 - 12io7
1700	1600	VCO 180 - 16io7



Symbol	Conditions	Maximum Ratings	
$I_{TRMS}$		280	A
$I_{TAVM}$	$T_C = 90^\circ\text{C}; T_{VJ} = 130^\circ\text{C}; 180^\circ \text{ sine}$	180	A
$I_{TSM}$	$T_{VJ} = 45^\circ\text{C}; t = 10 \text{ ms}$ (50 Hz)	4500	A
	$V_R = 0$ $t = 8.3 \text{ ms}$ (60 Hz)	4900	A
	$T_{VJ} = 125^\circ\text{C}; t = 10 \text{ ms}$ (50 Hz)	3800	A
	$V_R = 0$ $t = 8.3 \text{ ms}$ (60 Hz)	4200	A
$I^2t$	$T_{VJ} = 45^\circ\text{C}; t = 10 \text{ ms}$ (50 Hz)	101 000	A <sup>2</sup> s
	$V_R = 0$ $t = 8.3 \text{ ms}$ (60 Hz)	99 500	A <sup>2</sup> s
	$T_{VJ} = 125^\circ\text{C}; t = 10 \text{ ms}$ (50 Hz)	72 000	A <sup>2</sup> s
	$V_R = 0$ $t = 8.3 \text{ ms}$ (60 Hz)	73 000	A <sup>2</sup> s
$(di/dt)_{cr}$	$T_{VJ} = 125^\circ\text{C};$ repetitive, $I_T = 250 \text{ A}$ $f = 50 \text{ Hz}; t_p = 200 \mu\text{s};$	150	A/ $\mu\text{s}$
	$V_D = \frac{2}{3} V_{DRM};$ non repetitive, $I_T = I_{TAVM}$ $I_G = 0.5 \text{ A};$ $di_G/dt = 0.5 \text{ A}/\mu\text{s}$	500	A/ $\mu\text{s}$
$(dv/dt)_{cr}$	$T_{VJ} = 125^\circ\text{C}; V_D = \frac{2}{3} V_{DRM};$ $R_{GK} = \infty;$ method 1 (linear voltage rise)	1000	V/ $\mu\text{s}$
$P_{GM}$	$T_{VJ} = 125^\circ\text{C};$ $t_p = 30 \text{ ms}$	$\leq 10$	W
	$I_T = I_{T(AV)M};$ $t_p = 300 \text{ ms}$	$\leq 5$	W
$P_{GAVM}$		0.5	W
$V_{RGM}$		10	V
$T_{VJ}$		-40...+130	°C
$T_{VJM}$		150	°C
$T_{stg}$		-40...+125	°C
$V_{ISOL}$	50/60 Hz, RMS $t = 1 \text{ min}$	3000	V~
	$I_{ISOL} \leq 1 \text{ mA}$ $t = 1 \text{ s}$	3600	V~
$M_d$	Mounting torque (M4)	1.5 - 2.0	Nm
		14 - 18	lb.in.
Weight	Typical including screws	24	g

### Features

- Isolation voltage 3600 V~
- Planar glass passivated chips
- Low forward voltage drop
- Leads suitable for PC board soldering

### Applications

- DC Motor control
- Light and temperature control
- Softstart AC motor controller
- Solid state switches

### Advantages

- Easy to mount with two screws
- Space and weight savings
- Improved temperature and power cycling
- High power density
- Small and light weight

Data according to IEC 60747 and refer to a single diode unless otherwise stated.

IXYS reserves the right to change limits, test conditions and dimensions.

20170321a

© 2017 IXYS All rights reserved

1 - 2

Symbol	Conditions	Characteristic Values	
		typ.	max.
$I_D, I_R$	$V_R / V_D = V_{RRM} / V_{DRM}$ $T_{VJ} = 125^\circ\text{C}$		10 mA
$V_T$	$I_T = 200\text{ A}$ $T_{VJ} = 25^\circ\text{C}$		1.1 V
$V_{T0}$	For power-loss calculations only		0.75 V
$r_t$			1.23 mΩ
$V_{GT}$	$V_D = 6\text{ V}$ $T_{VJ} = 25^\circ\text{C}$		1.5 V
$I_{GT}$	$V_D = 6\text{ V}$ $T_{VJ} = -40^\circ\text{C}$ $T_{VJ} = 25^\circ\text{C}$ $T_{VJ} = -40^\circ\text{C}$		1.6 V 300 mA 400 mA
$V_{GD}$	$V_D = \frac{2}{3} V_{DRM}$ $T_{VJ} = 125^\circ\text{C}$		0.2 V
$I_{GD}$			10 mA
$I_L$	$t_p = 10\ \mu\text{s}$ ; $I_G = 0.5\text{ A}$ ; $di_G/dt = 0.5\text{ A}/\mu\text{s}$ $T_{VJ} = 25^\circ\text{C}$		450 mA
$I_H$	$V_D = 6\text{ V}$ ; $R_{GK} = \infty$ ; $T_{VJ} = 25^\circ\text{C}$		200 mA
$t_{gd}$	$V_D = \frac{1}{2} V_{DRM}$ $I_G = 0.5\text{ A}$ ; $di_G/dt = 0.5\text{ A}/\mu\text{s}$ $T_{VJ} = 25^\circ\text{C}$		2 μs
$R_{thJC}$	per thyristor; DC current		0.17 K/W
$R_{thJH}$		0.23	K/W
$d_s$	Creeping distance on surface		11.2 mm
$d_A$	Creepage distance in air		5.0 mm
$a$	Maximum allowable acceleration		50 m/s <sup>2</sup>

**Dimensions in mm (1 mm = 0.0394")**
