

Specification Status: Released

Electrical Rating

Voltage: 16V_{DC} MAX



Insulating Material:


Cured, Flame Retardant Epoxy Polymer

Lead Material:

20 AWG Tin Plated Copper
(0.8 mm [0.032] nom. diameter)

Part Marking:

 Manufacturer's Mark
 and Part Identification

 Lot Identification




TABLE I. INSTALLATION ENVELOPE DIMENSIONS:

| | A | | B | | C | | D | | E | | F | G | |
|-----|-----|--------|-----|--------|--------|--------|--------|-----|-----|--------|--------|-----|--------|
| | MIN | MAX | MIN | MAX | MIN | MAX | MIN | MAX | MIN | MAX | TYP | MIN | MAX |
| m | -- | 8.9 | -- | 14.1 | 4.3 | 5.8 | 7.6 | -- | -- | 3.0 | 1.2 | -- | 3.1 |
| in* | -- | (0.35) | -- | (0.56) | (0.17) | (0.23) | (0.30) | -- | -- | (0.12) | (0.05) | -- | (0.12) |

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS:

| CURRENT RATINGS | | | TIME TO TRIP | INITIAL RESISTANCE | | R ₁ MAX POST TRIP RESISTANCE STANDARD TRIP | R _A MAX | TRIPPED-STATE POWER DISSIPATION |
|--------------------|--------------|------|---------------------------|--------------------|--------|---|--------------------|---------------------------------|
| HOLD AT | AMPS AT 25°C | TRIP | SECONDS AT 25°C, 20 A MAX | OHMS AT 25°C | | OHMS AT 25°C | OHMS AT 25°C | WATTS AT 25°C TYP |
| R ₁ MAX | HOLD AT | | | MIN | MAX | | | |
| 4.0 | 3.0 | 7.6 | 2.0 | 0.0186 | 0.0390 | 0.061 | 0.085 | 2.5 |

Reference Documents:

PS400, PS300 (Ref for R₁ MAX)

Precedence: This

specification takes precedence over documents referenced herein.

Effectivity:

Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION:

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant

ELV Compliant

Pb-Free

Halogen Free*

Directive 2002/95/EC Compliant

Directive 2000/53/EC Compliant



*Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm.

TABLE III. AUTOMOTIVE SPECIFIC STRESS TESTS AND TEST CONDITIONS:

| ELECTRICAL STRESS TESTS | TEST CONDITIONS (see note 2) |
|--|----------------------------------|
| ESD Voltage Withstand (see note 1) | 25kV |
| Short Circuit Fault Current Durability | 25 cycles, 16V, 200A |
| Fault Current Durability | 350 cycles, 16V/100A |
| End-of-life Mode Verification | 1750 cycles, 16V/100A |
| Jump Start Endurance (see note 1) | 3 cycles, 26V, 1 minute duration |
| Load Dump Endurance (see note 1) | 10 cycles, 86.5V |

Note 1: The PolySwitch devices are tested in series with a load resistance and the voltages specified in the test conditions are shared between the PolySwitch device and the load resistance as specified in PS400.

Note 2: Please refer to Appendix A of PS400 for the detailed test procedures

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.