


# UNIVERSAL ROTARY SWITCHES



## Dimensions in mm



\* Dimensions shown for 72093, Dimensions may vary per part number

## Features and Benefits

- Control various circuit combinations through discrete output positions

## Specifications Overview

<b>Mounting:</b>	Hex Nut through 1/2 (12.7mm) 20 Panel Hole
<b>Housing:</b>	Plated Steel
<b>Voltage Rating:</b>	25A @ 12V DC 50A @ 12V DC
<b>Ingress Protections:</b>	O-Ring in Shaft See below for applicable part numbers

## Description

Littelfuse Rotary Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

Our Universal Rotary Switches are designed to provide circuit control to a multitude of power and accessory applications.

## Web Resources

Download 2D print and technical resources at:  
[littelfuse.com/UniversalRotarySwitches](http://littelfuse.com/UniversalRotarySwitches)

## Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles

## Ordering Information

PART NUMBER	DESCRIPTION	VOLTAGE RATING	INGRESS PROTECTION	ACTUATOR	POSITIONS	TERMINATION
72093	Five Position Universal Rotary Switch	25A at 12V DC	O-Ring in Shaft	None (D-Shaft)	5: Off - Hazard - Hazard & Headlight - Headlight & Work Light 1 - Headlight & Work Light 1 & Work Light 2	5 16AWG leads terminated in Aptiv Connector #2977042
72077	Four Position Universal Rotary Switch	50A at 12V DC	None	None (D-Shaft)	4: Off - 1,6,B - 1,2,3,6,B - 2,4,5,6,B	7 Screws
72077-09	Four Position Universal Rotary Switch	50A at 12V DC	O-Ring in Shaft	Cap with Arrow Directional Symbol	4: Off - 1,6,B - 1,2,3,6,B - 2,4,5,6,B	7 Screws