



RESISTANCE @ +25°C = 1,000 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "B"  
 BETA "β" (0 TO +50°C) = 2,941°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -3.3%/°C NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS NOMINAL  
 MAXIMUM TEMPERATURE RATING = +220°C

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	03/28/03	DD
"A"	LENGTH WAS 0.155" ± 0.010" & TAB THICKNESS WAS 0.019" ± 0.005"	03/28/03	DD

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com
DRAWN BY DAN DANKERT	
DATE 03/28/02	NTC THERMISTOR
REV. "A"	P/N SM102B1K
LAYER 0 OF 2	