



RESISTANCE @ +25°C = 10,000 NOMINAL  
 ACCURACY (0 TO +50°C) =  $\pm 1.0^\circ\text{C}$   
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA " $\beta$ " (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C =  $-4.4\%/^\circ\text{C}$  NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM  
 MAXIMUM OPERATING TEMPERATURE = +220°C

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	09/30/03	DD

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLL INS AVE. ORANGE, CA . 92867
DRAWN BY	DAN DANKERT	
DATE	09/30/03	NTC THERMISTOR P/N WM103J1B
REV.	NONE	
LAYER	0 OF 1	