



RESISTANCE @ +25°C = 100,000 Ω ± 4.78%
 ACCURACY @ +25°C = ± 1.0°C
 RESISTANCE/TEMPERATURE CURVE = "V"
 TEMPERATURE COEFFICIENT @ +25°C = -4.78%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +150°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

| | | | |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 05/03/07 | DD |
| REV | REVISION RECORD | DATE | APP |

| | | |
|----------|-------------|---|
| SCALE | NONE | U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA 92867 714-639-1000 www.ussensor.com |
| DRAWN BY | DAN DANKERT | |
| DATE | 05/03/07 | |
| REV | NONE | |
| LAYER | 0 OF 2 | |
| | | NTC THERMISTOR PROBE |
| | | P/N USP7806 |