



CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED



METRIC
COMPONENT

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE
MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD
A	03/20/09	006388R-RELEASE GMB		

COPIES TO	MATL SPEC	DESCRIPTION	QTY/M	U/M
1 9 18	CLEAR POLYCARBONATE (SEAL IS SILICON MVQ 40 ±5 SHORE A)			
2 10 19	FINISH			
3 12 20				
4 13 21	DRW GMB	DATE 03/20/09	SCALE	N/A
5 14 23	CHK	DATE	SUPER DR	
6 15 33		DATE	FINISH GOOD WT	GMB/PIECE
8 17 53	APPD	DATE		

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-TH1)	DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400
TOLERANCE		±0.05	±0.05	±0.1	±0.15	±0.2
3RD ANGLE PROJECTION						

TITLE: COVER

REVISION DRWG. NO: A 01520903U

OUTLINE

LITTELFUSE
DES. PLATES, ILLINOIS 60116