



METRIC
COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

LTR	DATE	REVISION	CHK	APD
A	20/Oct/18	516562GCC-NEW RELEASE FYUE		
B	16/Oct/17	517965GCC-DELETE DIMENSION 6.9 FYUE		

COPIES TO	MATL SPEC					
1 9 18	2.0mm MS PLATE					
2 10 19	FINISH					
3 12 20	ZINC CHROMATE PLATED (t = 3-8 microns)					
4 13 21	DRW FYUE					
5 14 23	DATE 20/Oct/16					
6 15 33	CHK					
7 16 43	DATE					
8 17 53	APPD					
	DATE					
	FINISH GOOD WT					
	GRAMS/PIECE					
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)						
DIMENSION	UP TO 0.5 - 3	OVER 3 - 6	UP TO 6 - 30	OVER 30 - 120	UP TO 120 - 400	OVER 400
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5
3RD ANGLE PROJECTION						
TITLE		METAL BRACKET				
		(for HWB18,12&6)				
LITTELFUSE		LIPA CITY, BATANGAS, PHILIPPINES				
REVISION		B			868-068	
DRWG. NO.		OUTLINE				